



All 3M Products Innovation Explore 3M

Search

United States [Change](#)

## Communication Technologies

[Products](#) | [Solutions by Network](#) | [Documents & Resources](#) | [Support](#)

[Where to Buy](#) [Contact Us](#)

[United States](#) > [All 3M Products](#) > [Market Segments](#) > [Electronics, Electrical, and Communications](#) > [Communication Technologies](#) > [Communication Technologies Product Catalog](#) > [Copper Connectors and Splices](#) > 3M™ Scotchlok™ IDC Full Pair/Drop Pair Inline Connector UDW2

# 3M™ Scotchlok™ IDC Full Pair/Drop Pair Inline Connector UDW2

3M ID 80611316508 UPC# 00051115191442 3M Product Number UDW2



[Like](#) | [Sign Up to see what your friends like.](#)

A sealed moisture-resistant, four-wire (1 full pair) inline aerial dropwire connector for copper or copper-coated steel conductors, the inline connector is for mid-span splices where strain-relief is provided.

Tape over-wrap is not required. It is recommended to use the 3M™ Scotchlok™ Crimping Tool E9BM for the UDW2 Connector.

• [Print](#)

**Need Help?** • [Share](#)

---

Questions? We can help  
[Contact Us](#)

[Overview](#) | [Documents](#)

### Specifications

Cable Type	PIC/Drop
Composition	Filled
Connector Type	Inline
Flame Retardant	No
Insulation Outside Diameter	0.175 Inch
Operating Temperature Range	-40 to 285 Degree Fahrenheit
Product Family	Scotchlok
Product Type	Connector
Wire Gauge	19 - 16 AWG

3M Communication Technologies: [Connect to MyTelecom](#) | [Where to Buy](#) | [Contact Us](#) | [View Mobile Site](#)

3M: [News](#) | [Careers](#) | [Investor Relations](#) | [MSDS Search](#) | [Transport Information Search](#) | [A-Z Product Index](#) | [Contact 3M](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2013. All Rights Reserved.

