



Main

Range	PratiKa
Product or component type	Socket
Device short name	PratiKa socket
Plug, socket category	Low voltage
Poles description	3P + E
Network type	AC
Outlet standard	Industrial

Complementary

Mounting mode	Panel-mounted
Plug, socket, control station shape	Angled
[In] rated current	32 A
[Ue] rated operational voltage	380...415 V
Network frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Self-extinguishing engineering polymer housing :
Contacts material	Brass sleeves :
Connections - terminals	Fast connection
Cable cross section	2.5...10 mm ²
Product weight	0.238 kg
Base dimension	90 x 100 mm
Height	100 mm
Width	90 mm
Depth	117 mm
Colour	Grey (RAL 7035)
Voltage colour	Red

Environment

Standards	IEC 60309-1 IEC 60309-2
IP degree of protection	IP44 conforming to IEC 60529

IK degree of protection	IK08 conforming to EN 62262
Fire resistance	850 °C conforming to IEC 60695-2-1
Relative humidity	50 % (40 °C) 70 % (30 °C) 90 % (20 °C)
Ambient air temperature for operation	35 °C (86400 s)

Contractual warranty

Warranty period	18 months
-----------------	-----------