

Datasheet

RS Pro Digital & Programmable HVAC Thermostat

RS Stock No: **823-4927**



Product Details

RS Pro plug in receiver is suitable for use with wireless thermostat and it fits in UK standard socket. You can plug in your heating appliance and control wirelessly for any part of your house. It can be programmed to work individually per appliance with internal dip switch, to select the address which matches the transmitter's address setting. If the transmitter's address does not match the receiver address, the receiver ignores the transmitter's message.

Features and Benefits

- Power source 240 V ac±13 A 50/60 Hz
- Relay contact rating voltage free 240 V ac/13 A
- Accuracy ±0.5°C
- Room temperature setting range of +5 to 35°C
- Storage temperature of -5 to 50°C
- Working frequency 868 MHz



Specifications:

Contact Rating	13 A
Contact Voltage	240 V ac
Maximum Temperature	+35°C
Minimum Temperature	+5°C
Supply Voltage	240 V ac
Temperature Range	+5 to +35°C