




© 1980 日本エー・エム・ピー株式会社
AMP 社の諸製品は特許又は特許出願中

© 1980 BY AMP (Japan) Ltd.
ALL RIGHTS RESERVED. AMP
PRODUCTS COVERED BY PATENTS
AND/OR PATENTS PENDING



回路番号
(CIRCUIT NO.)

キャビティマーク
(CAVITY MARK)

トレードマーク
(TRADE MARK)

- NOTES;
- 1, APPLIED CONTACT P/N: 170359, 170360, 170361, 170362
 - 2, MATING CONN: PLUG HOUSING P/N 172342
 - △ PANEL THICKNESS: 0.8 ~ 2.0 mm
 - 4, PRESS DIRECTION OF PANEL MUST BE SAME AS HOUSING INSERTED DIRECTION.
 - 5, INSTRUCTION SHEET: IS-105J
 - 6, PRODUCT SPEC: 108-5151

- 注:
1. 使用端子型番は 170359, 170360, 170361, 170362.
 2. 嵌合相手ハウジング型番は 172342
 - △ 適用パネル厚 0.8 ~ 2.0 mm
 4. 取付穴打抜方向とハウジングの挿入方向は同じとする
 5. 取扱説明書: IS-105J
 6. 適用製品仕様書: 108-5151

黄 (YELLOW)	1 - 172334 - 4
黒 (BLACK)	1 - -9
青 (BLUE)	1 - -6
緑 (GREEN)	1 - -5
赤 (RED)	1 - -2
自然色 (NATURAL)	172334 -1
色 (COLOR)	型番 (P/N)

A1	黄色追加 J-10297	TO M.S	7/28
A	変更 J-9972	AK	8/17
O	変更 J81-5998	R.Y.T	5/1
O	作成 J81-5957	R.Y.T	3/6
LTR.	変更 (REVISION RECORD)	DR.	CHK. DATE

寸法公差は ±0.20 (TOLERANCE: ±0.2)
パネル取付穴 (DIMENSION OF PANEL)

材料 (MATERIAL) 6/6 ナイロン (UL94V-2) (NYLON 6/6 UL94V-2)	一般公差 TOLERANCE ± 0.3 EXCEPT ± 1.0 AS NOTED	 日本エー・エム・ピー株式会社 TOKYO, JAPAN
仕上 (FINISH) 色: 表参照 HOUSING: SEE TABLE COLOR	DR. R. YUASA 4/20/81 CHK. J. Taniguchi 4/21/81 DE. APP.	
		SIZE B LOC J 番号 (NO.) C-172334
		尺度 (SCALE) 2:1 REV. A1 SHEET