




1

MAIN POLARIZING KEY

2.183
[55.45]

1.671
[42.44]

Ø 1.950
[49.53]
OVER KNURL

COUPLING RING

PLUG HOUSING

Ø 1.665
[42.29]

THREADED ADAPTER
(M35 X 1.75)

5

1

GROMMET

1

POLARIZING INDICATOR

HDP26-24-23SE-L015

DATE CODE

14K1411

1

6. PART MODIFICATION: THREADED ADAPTER

5

CONDUIT ADAPTER ACCEPTS EITHER TYPES:
A. CONDUIT ADAPTER CAP NUT (CN21) AND SEAL RING (SRN21)
B. BACKSHELL (M902-2243), COMPRESSION NUT (M902-2053), CABLE Ø .430-.570 [10.92-14.78]
C. BACKSHELL (M902-2244), COMPRESSION NUT (M902-2054), CABLE Ø .570-710 [14.78-18.03]

4

MATERIAL: PLUG HOUSING/COUPLING RING: PA66 GF10 (BLACK)
CONDUIT ADAPTER: PA66 GF10 (GREEN, GRAY, BLUE)
GROMMET: SILICONE (ORANGE-RED)

3

SEE 0425-021-0000 APPLICATION SPECIFICATION
A. RECOMMENDED WIRE INSULATION RANGE
B. CONTACT REMOVAL TOOLS

2. THIS PLUG MATES WITH HDP24-24XXP/SX-XXXX RECEPTACLE
X = SEAL TYPE (N,T,E)
XX = INSERT ARRANGEMENT
XXXX = MODIFICATION

1

SEE CUSTOMER DRAWING 0425-014-2400 FOR AVAILABLE INSERT ARRANGEMENTS AND PART NUMBERS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES[mm]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±.015 [0.38]
4 PLC ±
ANGLES ±0°30'0"

MATERIAL

FINISH N/A

DWN 19JAN1999
STEVE BEARD

CHK 15JAN2001
STEVE BEARD

APVD 15JAN2001
STEVE BEARD

PRODUCT SPEC
0425-021-0000

APPLICATION SPEC
3

WEIGHT

Customer Drawing

SCALE 1:1

TE Connectivity

NAME
PLUG, COUPLING RING
SIZE 24, -L015 MOD
HDP SERIES

SIZE A3

CAGE CODE 4AFU8

DRAWING NO. ©HDP26-24-XXP/SX-L015

RESTRICTED TO

SCALE 2:1

SHEET 1 OF 1

REV C