

# Spec-Kon® cable ties

## The right cable tie for the right application

### Characteristics


A complete range of cable ties for control panel applications.

- Available in different packaging quantities to respond to the user's need
- Available in different lengths and tensile strengths
- Sophisticated, ergonomic fastening installation tools and easy to use cable ties dispenser

### Technical Information

|                     |                             |
|---------------------|-----------------------------|
| Material            | Polyamide 6.6               |
| Temperature range   | -40°C to +85°C              |
| Colour              | Natural                     |
| Flammability rating | UL 94 V-2                   |
| Other properties    | Halogen free, Silicone free |

| Product Ref.   | Length L | Width W | Min. tensile strenght | Bundle Dia. from... to... | Quantity | Bags/ Carton |
|----------------|----------|---------|-----------------------|---------------------------|----------|--------------|
|                | [mm]     | [mm]    | [N]                   | [mm]                      | [pieces] |              |
| SKT100-80-100  | 100      | 2,5     | 80                    | 1.5 - 22                  | 100      | 550          |
| SKT100-80      | 100      | 2,5     | 80                    | 1.5 - 22                  | 1000     | 70           |
| SKT140-80-100  | 140      | 2,5     | 80                    | 1.5 - 33                  | 100      | 450          |
| SKT140-80      | 140      | 2,5     | 80                    | 1.5 - 33                  | 1000     | 55           |
| SKT160-80-100  | 160      | 2,5     | 80                    | 1.5 - 40                  | 100      | 400          |
| SKT160-80      | 160      | 2,5     | 80                    | 1.5 - 40                  | 1000     | 45           |
| SKT200-80-100  | 200      | 2,5     | 80                    | 1.5 - 53                  | 100      | 300          |
| SKT200-80      | 200      | 2,5     | 80                    | 1.5 - 53                  | 1000     | 32           |
| SKT140-180-100 | 140      | 3,6     | 180                   | 2 - 33                    | 100      | 300          |
| SKT140-180     | 140      | 3,6     | 180                   | 2 - 33                    | 1000     | 30           |
| SKT200-180-100 | 200      | 3,6     | 180                   | 2 - 53                    | 100      | 200          |
| SKT200-180     | 200      | 3,6     | 180                   | 2 - 53                    | 1000     | 22           |
| SKT300-180-100 | 300      | 3,6     | 180                   | 2 - 76                    | 100      | 120          |
| SKT300-180     | 300      | 3,6     | 180                   | 2 - 76                    | 1000     | 12           |
| SKT370-180-100 | 370      | 3,6     | 180                   | 2 - 102                   | 100      | 120          |
| SKT370-180     | 370      | 3,6     | 180                   | 2 - 102                   | 1000     | 12           |
| SKT188-220-100 | 188      | 4,8     | 220                   | 3 - 46                    | 100      | 160          |
| SKT188-220     | 188      | 4,8     | 220                   | 3 - 46                    | 1000     | 16           |
| SKT250-220-100 | 250      | 4,8     | 220                   | 3 - 60                    | 100      | 120          |
| SKT250-220     | 250      | 4,8     | 220                   | 3 - 60                    | 1000     | 12           |
| SKT300-220-100 | 300      | 4,8     | 220                   | 3 - 76                    | 100      | 80           |
| SKT300-220     | 300      | 4,8     | 220                   | 3 - 76                    | 1000     | 8            |
| SKT370-220-100 | 370      | 4,8     | 220                   | 3 - 102                   | 100      | 70           |
| SKT370-220     | 370      | 4,8     | 220                   | 3 - 102                   | 1000     | 7            |
| SKT300-540-100 | 300      | 7,6     | 540                   | 7 - 76                    | 100      | 50           |
| SKT300-540     | 300      | 7,6     | 540                   | 7 - 76                    | 500      | 10           |
| SKT370-540-100 | 370      | 7,6     | 540                   | 7 - 102                   | 100      | 40           |
| SKT370-540     | 370      | 7,6     | 540                   | 7 - 102                   | 500      | 8            |
| SKT750-540-50  | 750      | 7,6     | 540                   | 7 - #N/A                  | 50       | 30           |
| SKT776-780-50  | 776      | 9,0     | 780                   | 7 - 228                   | 50       | 30           |
| SKT912-780-50  | 912      | 9,0     | 780                   | 7 - 263                   | 50       | 10           |



# Spec-Kon® cable ties

## The right cable tie for the right application

### Characteristics

A complete range of cable ties for control panel applications.

- Available in different packaging quantities to respond to the user's need
- Available in different lengths and tensile strengths
- Sophisticated, ergonomic fastening installation tools and easy to use cable ties dispenser

### Technical Information

|                     |                                           |
|---------------------|-------------------------------------------|
| Material            | Polyamide 6.6                             |
| Temperature range   | -40°C to +85°C                            |
| Colour              | UV-resistant black                        |
| Flammability rating | UL 94 V-2                                 |
| Other properties    | UV-resistant, Halogen free, Silicone free |

| Product Ref.    | Length L | Width W | Min. tensile strenght | Bundle Dia. from... to... | Quantity | Bags/ Carton |
|-----------------|----------|---------|-----------------------|---------------------------|----------|--------------|
|                 | [mm]     | [mm]    | [N]                   | [mm]                      | [pieces] |              |
| SKT100-80X-100  | 100      | 2,5     | 80                    | 1.5 - 22                  | 100      | 550          |
| SKT100-80X      | 100      | 2,5     | 80                    | 1.5 - 22                  | 1000     | 70           |
| SKT140-80X-100  | 140      | 2,5     | 80                    | 1.5 - 33                  | 100      | 450          |
| SKT140-80X      | 140      | 2,5     | 80                    | 1.5 - 33                  | 1000     | 55           |
| SKT160-80X-100  | 160      | 2,5     | 80                    | 1.5 - 40                  | 100      | 400          |
| SKT160-80X      | 160      | 2,5     | 80                    | 1.5 - 40                  | 1000     | 45           |
| SKT200-80X-100  | 200      | 2,5     | 80                    | 1.5 - 53                  | 100      | 300          |
| SKT200-80X      | 200      | 2,5     | 80                    | 1.5 - 53                  | 1000     | 32           |
| SKT140-180X-100 | 140      | 3,6     | 180                   | 2 - 33                    | 100      | 300          |
| SKT140-180X     | 140      | 3,6     | 180                   | 2 - 33                    | 1000     | 30           |
| SKT200-180X-100 | 200      | 3,6     | 180                   | 2 - 53                    | 100      | 200          |
| SKT200-180X     | 200      | 3,6     | 180                   | 2 - 53                    | 1000     | 22           |
| SKT300-180X-100 | 300      | 3,6     | 180                   | 2 - 76                    | 100      | 120          |
| SKT300-180X     | 300      | 3,6     | 180                   | 2 - 76                    | 1000     | 12           |
| SKT370-180X-100 | 370      | 3,6     | 180                   | 2 - 102                   | 100      | 120          |
| SKT370-180X     | 370      | 3,6     | 180                   | 2 - 102                   | 1000     | 12           |
| SKT188-220X-100 | 188      | 4,8     | 220                   | 3 - 46                    | 100      | 160          |
| SKT188-220X     | 188      | 4,8     | 220                   | 3 - 46                    | 1000     | 16           |
| SKT250-220X-100 | 250      | 4,8     | 220                   | 3 - 60                    | 100      | 120          |
| SKT250-220X     | 250      | 4,8     | 220                   | 3 - 60                    | 1000     | 12           |
| SKT300-220X-100 | 300      | 4,8     | 220                   | 3 - 76                    | 100      | 80           |
| SKT300-220X     | 300      | 4,8     | 220                   | 3 - 76                    | 1000     | 8            |
| SKT300-540X-100 | 300      | 7,6     | 540                   | 7 - 76                    | 100      | 50           |
| SKT300-540X     | 300      | 7,6     | 540                   | 7 - 76                    | 500      | 10           |
| SKT370-540X-100 | 370      | 7,6     | 540                   | 7 - 102                   | 100      | 40           |
| SKT370-540X     | 370      | 7,6     | 540                   | 7 - 102                   | 500      | 8            |
| SKT750-540X-50  | 750      | 7,6     | 540                   | 7 - #N/A                  | 50       | 30           |
| SKT776-780X-50  | 776      | 9,0     | 780                   | 7 - 228                   | 50       | 30           |
| SKT912-780X-50  | 912      | 9,0     | 780                   | 7 - 263                   | 50       | 10           |

