

## Datasheet

**RS 12 Core Unscreened Industrial Cable, PVC Sheath, 6.4mm OD, 0.22 mm<sup>2</sup> CSA 1 A, 440 V, 25m**  
**Stock Number - 660-4059**



### Description:

**Rated Temperature (oC): -20 ~ 80**

**Rated Voltage (V):440**

**Flammability Test: IEC60332-1**



ENGLISH

**Construction:**

**Conductor: Tinned Copper**

**Conductor Dia. (mm):  $0.20 \pm 0.008$  x**

**7**

**Insulation: PVC**

**Insulation Dia. (mm):  $1.2 \pm 0.05$  x**

**12C**

**Tape: Mylar Spiral**

**Coverage:  $\geq 115\%$**

**ID Thread : Green, White/Green**

**A rip cord : 210 D**

**Jacket: FR-PVC**

**Outer Dia. (mm):  $6.1 \pm 0.1$**

**Colour:**

**The colour of the insulation: Red , Blue ,**

**Green , Yellow ,**

**White , Black , Brown , Violet , Orange , Pink ,**

**Light Green ,**

**Grey**

**The jacket colour: Black**

**Marking(3times/m):**

**RS 6604059 7 - 2 – 12A**

**Performance:**

**Electrical Characteristics:**

**Max.Conductor DC Resistance at  
20°C (  $\Omega$ /Km ) :**  
**<92**

**Min.Insulation DC Resistance at 20°C  
(  $M\Omega$ \*KM ) :**  
**>200**

**Current Rating : 1 A**

