



TYC28MX

Premium cable tie with stainless steel locking barb - Polyamide 12 UV-resistant version, remains flexible in cold & dry environments.

T&B Catalog Number: TYC28MX
EAN Number: 05414363067207
UPC Number: 78621084802
Description: Premium, standard cable tie, 360 x 4.8 mm, black Polyamide 12 UV-resistant



**BUREAU
VERITAS**

Technical Information

Type	standard
Material	Polyamide 12 UV-resistant
Material Locking Barb	316 grade stainless steel
Temperature Range	-40°C to +85°C
Flammability Rating	UL 94 V-2
Colour	black
Halogen free	yes
Silicone free	yes
UV-resistant	yes

Approvals

Other approval: BVQ

Ordering Information

Length (mm)	360
Width (mm)	4.8
Thickness (mm)	1.1
Max. Bundle Diameter (mm)	102
Min. Bundle Diameter (mm)	3.5
Min. Tensile Strength (N)	150
Quantity (pieces)	1000
Packaging Type	bag
Tooling	ERG50, ERG120, WT193A