

ToLEDo Ball 3W Satin 827 E27 SL

0126299



Range features



PRODUCT OVERVIEW

Ordering number	0126299
Technology	LED
Light colour	827 Homelight
Energy class	A++
Average life (Rated) (h)	15000
Lamp shape	Ball
Lamp finish	frosted
Dimmable	No
Cap/Base	E27
Type	ToLEDo Ball
EAN code	5410288262994
CRI (Ra)	80
Colour temperature (K)	2700
Useful luminous flux (Rated) (lm)	250
Efficacy (Rated) (lm/w)	83
Watt (Nominal) (W)	3
Equivalent watt (W)	25
Voltage (V)	220-240

ToLEDo Ball 3W Satin 827 E27 SL

0126299

DATA TABLE

General data

Ordering number	0126299
Dry applications use only	Yes
Technology	LED
Average life (Rated) (h)	15000
Energy saving lamp	Yes
Energy class	A++
Average life (Nominal) (h)	15000
Lamp finish	frosted
Lamp shape	Ball
Dimmable	No
Cap/Base	E27
Type	ToLEDo Ball
EAN code	5410288262994
Product name	ToLEDo Ball 3W Satin 827 E27 SL
Lamp mercury content (mg)	0
Starting time (max) (s)	0.05
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Control gear required	No
Fixture rating	Open
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	>7500
Special purpose lamp	No
Transformer required	No
Sales pack quantity	1
Optimal operating condition (°C)	25

Optical data

Light colour	827 Homelight
CRI (Ra)	80
Suitable for accent lighting	No
Colour temperature (K)	2700
Useful luminous flux (Rated) (lm)	250
Luminous flux (Nominal) (lm)	250
Lumen maintaining at end of nominal Life (lm)	70
Chromaticity coordinate Y	-1
Chromaticity coordinate X	-1
Adjustable chromaticity	No

ToLEDo Ball 3W Satin 827 E27 SL

0126299

Electrical data

Efficacy (Rated) (lm/w)	83
Watt (Rated) (W)	3
Watt (Nominal) (W)	3
Equivalent watt (W)	25
Voltage (V)	220-240
Lamp power factor	0.35

Physical data

Lamp Length (mm) - C/L	90
Lamp Diameter (mm) - D	45
Lamp dimension equal to filament lamp equivalent	Yes

ToLEDo Ball 3W Satin 827 E27 SL

0126299

TECHNICAL DRAWINGS

