



Price* : 14.22 GBP



Main

| | |
|--|------------------------------|
| Range | Lineryg |
| Product name | HK |
| Product or component type | Plug outlet |
| Poles description | 3P |
| [I _{th}] conventional free air thermal current | 32 A |
| I ² t on activation | 200000 A ² .s |
| Number of points | 2 |
| Number of cables | 3 cable(s) 4 mm ² |
| Cable length | 0.25 m |
| Quantity per set | Set of 6 |

Complementary

| | |
|-------------------------------|--|
| [Ui] rated insulation voltage | 600 V conforming to UL 690 V conforming to IEC 60439-1 600 V conforming to CSA |
| Peak current | 25 kA |
| Width | 18 mm |
| Height | 45.5 mm |
| Depth | 38 mm |
| Product weight | 0.045 kg |

Environment

| | |
|------------------------|--|
| Standards | IEC 60439 |
| Product certifications | CSA DNV LROS (Lloyds register of shipping) UL |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0713 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|