

Datasheet

## RS Pro Natural Nylon Screw Mount Cable Tie, 171.5mm x 3.7 mm

RS Stock No: **601-085**



### Product Details

RS Pro nylon 66 screw mount cable tie in natural colour, measures 171.5 x 3.7 mm. It comes with a screw mounting hole and is suitable for binding cable or components and securing them in position. The cable tie can be secured to panel with a single bolt.

### Features and Benefits

- Non-releasable
- Flammability rating UL94V-2
- Screw mount cable tie



ENGLISH

### Specifications:

|                               |  |
|-------------------------------|--|
| Colour                        | Natural                                    |
| Fire Behaviour                | Flame Retardant                            |
| Length                        | 171.5 mm                                   |
| Material                      | Nylon 66                                   |
| Maximum Bundle Diameter       | 40 mm                                      |
| Maximum Operating Temperature | +85°C                                      |
| Minimum Operating Temperature | -40°C                                      |
| Operating Temperature Range   | -40 to +85°C                               |
| Product Name                  | Cable Tie                                  |
| Quantity                      | 100  |
| Standards Met                 | UL 94 V-2, cURus, ABS, DNV, RoHS Compliant |
| Tensile Strength              | 176.4 N                                    |
| Type                          | Screw Mount                                |
| Width                         | 3.7 mm                                     |