


AMP WIRE RANGE	 Listed	 LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED



- 1 STAMP AMP 16-14* APPROX AS SHOWN
- 2 WIRE INSULATION DIA: .115-.170
- 3 TONGUE MATERIAL THK: 0.79 ± 0.05 [.031 ± .002]
- 4 PVC COLOR: BLUE
- 5 PVC COLOR: BLACK
- 6 REPLACED BY 34163

OBSOLETE	25	LOOSE PIECE, BAG	4	8-34163-5
	100	LOOSE PIECE, BOX	4	8-34163-1
6 OBSOLETE	-	LOOSE PIECE	5	2-34163-2
	4000	ON TAPE, REEL	4	2-34163-1
	-	LOOSE PIECE	4	34163

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 90°C MAX	QUANTITY		PACKAGE TYPE		PART NO	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: NOT APPLICABLE	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20[.008] 3 PLC DEC ± - ANGLES ± -	DR 08/06/92 DK SCHRUM	AMP AMP Incorporated Harrisburg, PA 17105-3608			
	FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] SOLID OR STRANDED		CHK 11/10/92 RE HERSEY				
					APPD 11/10/92 ML ELLIS	NAME			
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL COPPER PER ASTM B-152 PVC COLOR, SEE TABLE	APPD 11/10/92 M BARNABA	TERMINAL, RING TONGUE, PLASTI-GRIP™			
				FINISH TIN PLATE PER MIL-T-10727	PRODUCT SPEC 108-1034				
						APPLICATION SPEC NOT AVAILABLE	SIZE B	CAGE CODE 00779	DRAWING NO C-34163
					WEIGHT -	SCALE 4:1	SHEET 1 OF 1		