

Datasheet

RS 5 pairs , 100m CW1128 Telecom Cable Black Sheath

Stock Number - 520-2784



Description:

Rated Temperature (oC): -20 ~ 70

Rated Voltage (V):240



ENGLISH

Construction:

Conductor: Bare Copper

Conductor Dia. (mm): 0.50 ± 0.01

Insulation: Skin-FPE-Skin

Insulation Dia. (mm): $0.9 \pm 0.03 \times 2C$

Twist x 5P

Jelly Filled

Tape : Mylar Sprial

Jacket: PE

Outer Dia. (mm): 7.8 ± 0.25

Colour:

The colour of the insulation: White,

Blue ; White ,

Orange ; White , Green ; White , Brown

; White , Grey

The jacket colour: Black

Marking(3times/m):

RS 5202784 CW 1128 TELECOM 5PR

Performance:**Electrical Characteristics:**

Max.Conductor DC Resistance at 20°C (Ω /Km) :
<96

Min.Insulation DC Resistance at 20°C ($G\Omega$ *KM) :
>1.5

Mutual capacitance (at 800Hz) (nF/KM) : <64

Pair-to pair capacitance unbalance (at 800Hz)(pF/500M) : 275

