

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **31403-3700**
Status: **Active**
Overview: MX64™ Sealed Single Row Connectors
Description: 2.54mm MX64™ Sealed Single Row Crimp Housing, MX64™ Terminal, Black, 3 Circuits, Mating Part: Keying D, without CPA Lock

Documents:

[3D Model](#) [Application Specification AS-31402-000 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-31402-000 \(PDF\)](#)

General

Product Family	Crimp Housings
Series	31403
Application	Power
More Detailed Tech Information	http://ewcap.uscarteams.org
Overview	MX64™ Sealed Single Row Connectors
Product Name	MX64™, USCAR
UPC	822348792955

Physical

Circuits (maximum)	3
Color - Resin	Black
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Resin	Modified Polystyrene Alloy, Polyester
Net Weight	4.762/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	10A
-------------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-31402-000
Product Specification	PS-31402-000
Sales Drawing	SD-31402-211



image - Reference only

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

31403Series

Mates With

Sensors, Other USCAR Interfaces

Use With

Molex MX64™ Terminals [33467](#) , [33468](#)