

COMB BINDING

Of the many binding systems available, comb binding is by far the most popular. Quick and simple, comb binding suits a wide variety of user needs. It also offers total flexibility, and you can bind the smallest document or a 450 page report with ease.

Comb binding is also a very practical binding method. Comb bound documents open out completely flat so they are ideal for presentations and easy to photocopy. The pages are completely secure yet easy to update, as sheets can be added or deleted when required.

Rexel comb binders make life even easier for you. They punch many more pages than other systems, yet require less effort. Documents can be bound much more quickly too, because of the unique, separate comb opening mechanism. The robust, all metal chassis and mechanism means you can use a Rexel comb binder day after day with superb results every time.

Rexel offers a comb binding system to meet every binding requirement, from a compact budget machine to the convenience of electric punch models. All will create professional documents in a matter of minutes.



Comb Binder overview

Model	Code	Max Punch Capacity (sheets)	Max Binding Capacity (sheets)	Max Comb Size	Formats	Adjustable Edge Guide	Comb Size Guide	Adjustable Margin Control	Punch Selection	Dual Binding	TIPS Punching System
Bindmate	4490000	6	40	8mm	A4	-	-	-	-	-	-
CB205	2100405	8	140	16mm	A4	yes	yes	-	-	-	-
CB255	2100642	15	175	20mm	A4	yes	yes	-	-	-	-
CB305	2100565	15	175	20mm	A4	yes	yes	-	-	-	-
CB355	2100566	25	450	50mm	A4	yes	yes	-	-	-	yes
CB355E	2100567	25	450	50mm	A4	yes	yes	-	-	-	yes
CB405	2100568	30	450	50mm	A4,A5	yes	yes	yes	yes	yes	yes
CB405E	2100569	30	450	50mm	A4,A5	yes	yes	yes	yes	yes	yes