





M	EX-AR
---	-------



NOTES

- NOTES
- 1 - EXPLOSION PROOF - UNDERWRITERS LAB INC LISTED FOR HAZARDOUS LOCATIONS
NEMA 7, CLASS I, GROUPS C AND D, NEMA 9, CLASS II, GROUPS E, F, AND G
 - 2 - 8X MOUNTING SCREW HOLE, 10-32 UNF THREADS X (.219) DEEP
 - 3 - 8-32 UNC X (.219) TERMINAL SCREWS AND CUPWASHERS
 - 4 - EUROPEAN HAZARDOUS LOCATIONS DESIGNATION: EEx d IIB + H2 T6 CATAGORY II 2 G
 - 5 - SEAL RATING: NEMA 1

- 
 EXTERNAL GROUND SCREW MAY BE ASSEMBLED TO ANY UNUSED MOUNTING SCREW HOLE

 ASSEMBLE PROVIDED SPLIT LOCKWASHER BETWEEN GROUND LUG AND HOUSING

CHARACTERISTICS	ELECTRICAL DATA
OPERATING FORCE ----- 1/2 - 1 1/4 LB	CONTACT ARRANGEMENT
RELEASE FORCE ----- 1/4 LB MIN	S P D T
PRETRAVEL ----- .219 MAX 8°	L96
DIFFERENTIAL TRAVEL --- .007 MAX 1/4°	15A 125, <u>250</u> OR 480 VAC
DO NOT OVERTRAVEL MORE THAN --- 90°	1/8HP 125 VAC, 1/4HP <u>250</u> VAC
SWITCH - BASIC REPLACEMENT--BZ-2R-P4	1/2A 125 VDC, 1/4A 250 VDC
	  

MASTER REDUCED
ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 81828

SWITCH – ENCLOSED

CATALOG LISTING

EX-AR

THIRD ANGLE PROJECTION		
		
SCALE FULL		
DO NOT SCALE PRINT		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ONE PLACE	(.0)	$\pm .030$
TWO PLACES	(.00)	$\pm .015$
THREE PLACES	(.000)	$\pm .005$
ANGLES		$\pm$
WEIGHT		