

LED LENSER® K2 Mini Key-Light

High quality everyday LED key-light made from strong aircraft-grade aluminium. Though minute it is a touch larger than some other micro-sized lights and this extra size equates with bigger output: a beam distance up to 20 metres with a maximum 25 lumens brightness. Not bad for a teeny torch the size of a finger and weighing only 20g. It makes it a helpful source of short-distance light, useful for finding things hidden under the bed, for lighting up key holes or even checking your footing in slippery conditions. Turn it on with a deliberate twist-action, a feature which makes it less likely to come on by accident in your pocket. Even if it does the generous 5 hour burn time should keep this mini key-light going for longer than others. Batteries: 4 x AG3 (included).

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Powerful mini key-light
- Energy efficient LED Light Chip
- Reliable German engineering
- Smart, yet robust aluminium casing
- Twist on-off switch
- Water and dust resistant. IPX54

Technical Information

Size: 60 x 14mm Ø

Power: 25 lumens max

Run Time: up to 5 hours

Beam Distance: up to 20m

Weight: 20grams

Supplied with : Batteries (4xAG13)