



ENGLISH

Datasheet

Stock No: 213-152

RS Pro HSS 6.8mm Jobber Drill Bit



Product Details

Metric HSS Twist Drill Bits

Metric high speed twist drills for metal, wood and plastic drilling.

Perfect for general purpose workshop and maintenance drilling work

High Speed Steel (HSS) construction, ideal for use with power tools

Black finish for corrosion and wear protection

Standards

DIN 338

HSS Ground Flute

Steel Jobber Drills Individual

Manufactured to DIN 338

Various point angles

Ideal for general workshop or maintenance use where precision and high productivity are not required

Popular sizes available in drums containing 50 drills



ENGLISH

Specifications:

Diameter	6.8mm
Type	Jobber
Material	HSS
Overall Length	109.5 mm
Shank Size	6.8mm
Shank Type	Plain
Point Angle	118°