

# Specifications for BMP41/BMP51/BMP53 Labelmaker Tape

|                                  |  |
|----------------------------------|--|
| <b>Adhesive</b>                  | Permanent Acrylic  |
| <b>Application</b>               | Indoor & Outdoor Grade Facility & Safety Identification  |
| <b>Article No.</b>               | 143371   |
| <b>Brady Material No.</b>        | <a href="#">B-595</a>  |
| <b>Material Type</b>             | Vinyl  |
| <b>Colour</b>                    | Black on White   |
| <b>Finish</b>                    | Gloss  |
| <b>Laboratory Application</b>    | Well Plates;General Identification   |
| <b>Description</b>               | Durable, low-shrink vinyl with our most aggressive adhesive. Conforms to irregular, curved, rough and highly textured surfaces (painted cinder blocks, uneven wood, textured plastics, paper jacketed pipes, powder coated surfaces). Also adheres to difficult low energy surface items (PVC piping, blow-moulded equipment cases, ABS plastics, recycled plastics) |
| <b>Max. Service Temp. °C</b>     | 82   |
| <b>Order Reference</b>           | MC-500-595-WT-BK   |
| <b>Printer Compatibility</b>     | BMP41; BMP51; BMP53  |
| <b>Shape</b>                     | Continuous   |
| <b>Size - Length (m)</b>         | 7.62   |
| <b>Size - Width (mm)</b>         | 12.70  |
| <b>Total Qty per Pack</b>        | 1 Label(s) / Box   |
| <b>Voice/Data Application</b>    | Broadcast Patch Bay Strips; Faceplate & Outlet; Punch Block & Patch Panel; Non-Adhesive Slide-in Strips  |
| <b>Industry</b>                  | Data & Telecommunications; Electrical; Facility & Safety Industry; Process   |
| <b>Layout</b>                    | Continuous Roll  |
| <b>Min. Application Temp. °C</b> | -18  |
| <b>Min. Service Temp. °C</b>     | -40  |
| <b>Thickness (mm)</b>            | 0.1  |