

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19432-0014

Status:

Active

Overview:

MX150L™ Industrial Sealed Connector System

Description:

MX150L™ 2 Circuit Female Sealed Receptacle for 8 AWG Wire

Documents:

3D Model

Drawing (PDF)

Product Specification PS-19432-001 (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification

CSA

UL

LR18689

E152602

General

Product Family

Series

Application

Comments

Crimp Housings

19432

Power, Wire-to-Wire

Mat Seal Color is Red, Polarized to Mating Part.
IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec

Overview

Product Literature Order No

Product Name

UPC

MX150L™ Industrial Sealed Connector System

987650-2181

MX150L™

822350191517

Physical

Circuits (maximum)

Circuits Detail

Flammability

Gender

Glow-Wire Compliant

Keying to Mating Part

Lock to Mating Part

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

2

1x1

94V-0

Female

No

N/A

Yes

13.432/g

1

Bag

No

5.84mm

Yes

No

-40°C to +125°C

Electrical

Current - Maximum per Contact

40A

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19432-001

SD-19432-001



image - Reference onlySeries

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19432Series

Mates With

19433-0014 Male Plug

Use With

19434 Female Terminals

This document was generated on 10/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION