

Kabelbinder SL-HT

Aussenanwendung, höhere Temperaturen,
Innenzahnung

PA 6.6 schwarz HT



SES®-QUICK
-40 bis +110°C



• Kabelbinder SL HT

Aussenanwendung, höhere Temperaturen, UV-beständig

Typ	Art. Nr.	Abmessungen Länge x Breite mm	max. Bündel-Ø mm	Mindest- Reisskraft daN	
85/24 SL HT-M	0186 0110 010	85 x 2,4	16	8	1000
85/24 SL HT-C	0186 0111 010	85 x 2,4	16	8	100
100/25 SL HT-M	0186 0120 010 *	100 x 2,5	20	8	1000
100/25 SL HT-C	0186 0121 010	100 x 2,5	20	8	100
150/26 SL HT-M	0186 0122 010	150 x 2,6	40	8	1000
150/26 SL HT-C	0186 0123 010	150 x 2,6	40	8	100
200/26 SL HT-M	0186 0180 010 *	200 x 2,6	50	8	1000
200/26 SL HT-C	0186 0181 010	200 x 2,6	50	8	100
145/34 SL HT-M	0186 0130 010 *	145 x 3,4	35	13	1000
145/34 SL HT-C	0186 0131 010	145 x 3,4	35	13	100
210/34 SL HT-M	0186 0142 010	210 x 3,4	55	13	1000
210/34 SL HT-C	0186 0143 010	210 x 3,4	55	13	100
300/36 SL HT-M	0186 0232 010	295 x 3,6	76	13	1000
300/36 SL HT-C	0186 0233 010	295 x 3,6	76	13	100
370/36 SL HT-C	0186 0242 010	370 x 3,6	102	13	100
160/46 SL HT-M	0186 0124 010	160 x 4,6	38	22	1000
160/46 SL HT-C	0186 0125 010	160 x 4,6	38	22	100
185/46 SL HT-M	0186 0140 010	185 x 4,6	47	22	1000
185/46 SL HT-C	0186 0141 010	185 x 4,6	47	22	100
250/46 SL HT-M	0186 0126 010	250 x 4,6	60	22	1000
250/46 SL HT-C	0186 0127 010	250 x 4,6	60	22	100
300/46 SL HT-M	0186 0146 010	300 x 4,6	83	22	1000
300/46 SL HT-C	0186 0147 010	300 x 4,6	83	22	100
380/47 SL HT-C	0186 0150 010	380 x 4,7	109	22	100
180/76 SL HT-C	0186 0132 010	180 x 7,6	36	54	100
240/76 SL HT-C	0186 0144 010	240 x 7,6	50	54	100
300/76 SL HT-C	0186 0148 010	300 x 7,7	76	54	100
365/76 SL HT-C	0186 0160 010	365 x 7,6	100	53	100
550/90 SL HT-C	0186 0163 010	550 x 8,9	155	79	100
780/90 SL HT-C	0186 0162 010	775 x 8,9	230	79	100

* Geliefert in 10 Bündeln à 100 Stück.

