


DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION




NOTES:

- 1 FOR USE ON MINIATURE APPLICATORS (LEFT-RIGHT FEED)
AMP-O-MATOR APPLICATION.

2 DIM $0,81^{+0,04}$ TO BE MEASURED OVER A LENGTH 7,5mm
AS INDICATED

3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

UNPUBLISHED DRAWING : AMP RIGHTS RESERVED
This drawing is supplied to.....
.....for use by
.....
or its nominated suppliers for the purpose
of inspecting AMP-PRODUCTS.
AMP-HOLLAND B.V.
DATE.....
SIGNATURE.....



3 OBSOLETE

UNPLATED

PH. BRONZE

160645-3

TINPLATED

BRASS

160645-2

UNPLATED

BRASS

160645-1

FINISH

MATERIAL

PARTNUMBER

RESTRICTED CUSTOMER FOR REFERENCE ONLY
WILL NOT BE UPDATED

© COPYRIGHT 19- BY AMP HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE
COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.

THIS DRAWING IS UNPUBLISHED
RELEASED FOR PUBLICATION 19

AMP

AMP HOLLAND B.V.
's-Hertogenbosch,
The Netherlands.

01	REV PER ECO-10-000444	KK	AEG	09JAN10
0	EH-0933-97	D.K.	R.V.	27 AUG 97
LTR.	REVISION RECORD	DR.	CHK.	DATE

DR.: D. KESSLER
DATE: 27 AUG 97

CHK.: R. VOS
DATE: -

APP.: -
DATE: -

DWG.No.
C-160645

REV.LTR.
01

SHEET
1 OF 1

A3