

## Cable protection end sleeve - WP-SC PA HF 15,8 BK - 3240983

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




End sleeves as cable protection

Image shows WP-TS PA HF 10.0 BK version



### Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 711012
Weight per Piece (excluding packing)	1.56 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	20 mm
Inner diameter (f)	10.30 mm
Outside diameter	15.80 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

#### General

Color	black
Components	Halogen-free
Inflammability class according to UL 94	V0
Material	PA

# Cable protection end sleeve - WP-SC PA HF 15,8 BK - 3240983

## Classifications

### eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC002584
ETIM 5.0	EC002584

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

## Approvals

### Approvals

---

#### Approvals

UL Recognized / LR

---

#### Ex Approvals

---

Approvals submitted

---

### Approval details

UL Recognized
---------------

LR
----

---

