


LOC	DIST	REVISIONS					
IJ	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	INITIAL ISSUE	13 SEP 05	MGR	DB



- NOTES:
- 1 ATTENUATION $\leq 0,3$ dB, MEASURED AT 1300nm ACC. TO IEC 61300-3-4 EQUILIBRIUM MODE CONDITION
 - 2 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH INDIVIDUALLY PACKED ASSEMBLY
 - 3 CABLE INFO:
 - CORE DIA — 50/125 μm
 - OUTER DIA — 2,5 mm
 - JACKET COLOR — ORANGE
 - JACKET MATERIAL — LSZH

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-5349560-Y	XY,0
4-5349560-1	1,5 -0/+0,2
9-5349560-1	15,5 -0/+0,2

2	—	PROTECTIVE COVER, 2.5MM, BLACK	5
2	—	KIT, MM, CER, ASSY, BULK	4
2	—	CRIMP EYELET, BRIGHT TIN	3
2	—	FOAC STRAIN RELIEF 2,5 BAY BLACK	2
L	—	FOCAB 2.5S 50/125 ORANGE LSZH	1
Qty	Part Number	Description	Item
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 13 SEP 05 CHK 13 SEP 05 APVD 13 SEP 05 PRODUCT SPEC APPLICATION SPEC WEIGHT — CUSTOMER DRAWING	GIRIYAPPA. M DIWAKAR BELAVADI DIWAKAR BELAVADI FOOM50 LEAD 2,5S ST — ST A200779C=5349560 SCALE NTS SHEET 1 OF 1 REV A
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH —	NAME Tyco Electronics Corporation FOBU, Bangalore, India
MATERIAL —		RESTRICTED TO —	