

**SOLID PC 2819 18 T**



Sample photo

**Order symbol:** PC 2819 18 T  
**Product nbr:** 5330070  
**Description:** Enclosure, PC  
**Remarks:** Transparent cover

**EAN:** 6418074005458  
**El. number:**  
 Finland: 3423807  
 Italy: 7402025  
 Sweden: 2539442

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		278	188	180	Ingress Protection (EN 60529): IP 66/67
<b>inch:</b>		10.9	7.4	7.1	Impact Resistance (EN 62262): IK 08/09
<b>Materials:</b>					
<b>Material:</b>		Polycarbonate			Electrical insulation: Totally insulated
<b>Base colour:</b>		RAL 7035			Halogen free (DIN/VDE 0472, Part 815): Yes
<b>Cover colour:</b>		Clear transparent			UV resistance: UL 508
<b>Cover screws material:</b>		Polyamide			Flammability Rating (UL 746 C 5): UL 94 5V
<b>Cover screws colour:</b>		Grey			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Gasket material:</b>		Polyurethane			NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12
<b>Temperatures:</b>					
<b>Short term:</b>		-40 ... 120 °C			<b>Certificates:</b> Underwriters Laboratories Fimko Europe EN 62208: 2003 UL Canada Gost R
<b>Continuous:</b>		-40 ... 80 °C			
<b>Short term:</b>		-40 ... 250 °F			
<b>Continuous:</b>		-40 ... 175 °F			
<b>Accessories:</b>					
EKJVT		Mounting plate			
EKV 12		DIN-35 Mounting rail			
EKV 22		DIN-35 Mounting rail			
EKJZR		Extension frame			

