


REV	DESCRIPTION	DATE
-----	-------------	------

NOTE:

1. MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16
AMP.	9	12	17	18
2. MAXIMUM ELECTRICAL RATING:
125°C 300 VOLTS MAX.
3. INSULATION MATERIAL: PC
4. INSULATION COLOR: RED
5. TERMINAL MATERIAL: BRASS
6. WIRE RANGE: 22-16A.W.G. (0.5-1.5mm²)
7. NEMA TAB: .032*.250 (0.8*6.35)

Tolerance Unless Otherwise Specified	
0 >	mm ±
>	mm ±
>	mm ±
>	mm ±
>	mm ±
	ANGLE
	° REF ±
	° ±
	° ±

NAME	PC-INSULATED MALE DISCONNECTORS				UNIT	mm	
PART NO.	MDN11-250	MATERIAL			APPROVE		
NUMBER	TZV-055	SCALE	SHEET	PAGE	CHECKED		
DATE	09/07/2005	4 : 1	1-0	1 OF 1	DRAWN		