

HUBER+SUHNER® DATA SHEET

Coaxial PCB Connector: 82_MBX-50-0-4/113_N

Rev.: D



Description

Straight PCB jack

Interface Standards
HUBER+SUHNER MBX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type through holes
Weight 0.001714 kg

Environmental Data

Operating Temperature -55 °C to 155 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Centre contact
Outer contact
Body
Insulator

Material

Brass
Brass
Brass
LCP

Surface Plating

SUCOPRO Plating
SUCOPRO Plating
SUCOPLATE (R) Plating

Related Documents

Outline drawing DOU-00144735
Catalogue drawing DCA-00161472
Mounting hole DPA-00144881

Ordering Information

Tape and Reel package 82_MBX-50-0-4/113_NM
Bulk 100 pcs package 82_MBX-50-0-4/113_NH
Single package 82_MBX-50-0-4/113_NE

Remarks

PCB connector with stand-offs

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.

HUBER+SUHNER – Excellence in Connectivity Solutions



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com