

Cam rollers



Dimensions			Basic load ratings		Fatigue load limit	Maximum radial loads		Limiting speed	Mass	Designation
D	d	B	dynamic C	static C ₀	P _u	dynamic F _r	static F _{0r}			
mm			kN		kN	kN		r/min	kg	-
80	35	27	34,5	21,6	0,915	16,6	24	4300	0,64	305807 C-2Z

