

Datasheet

## RS Pro 86dB sound Panel Mount Square Wave External Piezo Buzzer

RS Stock No: **771-6926**



### Product Details

RS Pro external piezo buzzer operates at voltages up to 30 V. This square wave buzzer delivers 86 dB sound at frequencies up to 2500 Hz. It is suitable for applications that require high sound output.

### Features and Benefits

- Circular cased flanged mounting transducer
- Flying lead connections
- High sound output
- External circuitry required for operation

**Specifications:**

Drive Type	External
Mounting Type	Panel Mount
Tone Type	Square Wave
Capacitance	30 nF
Diameter	30 mm
Dimensions	30 (dia.) x 40 x 9.5 mm
Height	9.5 mm
Length	40 mm
Maximum Frequency	2500 Hz
Maximum Operating Temperature	+85°C
Maximum Supply Voltage	30 V dc
Minimum Operating Temperature	-30°C
Sound Level	86 dB
Supply Current	9 mA