




Product information STASAP 5 grau/grey

Industrial Connecting Solutions:Rectangular Connectors:Power Connectors (ST series):Surface mounted connector:STASAP 5 grau/grey

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-24351-24357-36016/en/conf/ui/istate>

Name	STASAP 5 grau/grey
	
	Surface mounted connector, not assembled with added contacts
Delivery informations	
Availability	available
Product description	
Description	Surface mounted connector, not assembled with added contacts
Type	STASAP 5 grau/grey
Order No.	932 512-106
Type of contact	male
Number of contacts	5 + PE
Conductor size	max. 1 mm ²
Housing Color	grey
Contact bearer color	black
Technical data	
Pin dimensions	1.6 mm
Rated voltage	AC 400 V / DC 250 V
Rated current	DC 10 A / AC 6 A
Contact resistance	<= 10 mOhm
Type of termination	screws
Mounting	Schrauben
Material	
Contact material	Cu Zn
Contact surface material	Ag
Contact bearer material	PA
Housing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 54
Pollution severity	3
Temperature range	-30 °C to +90 °C
Inflammability class	
Housing	UL 94 HB
Contact bearer	UL 94 V-0
Approvals	
VDE	VDE
SEV	SEV
Packing unit	
Packaging unit	100 pieces
Scope of delivery and accessories	
Accessories to order separately	safety brackets STASI 3, order no. 732 045-001

