

## Cable - FLK 40/4X14/EZ-DR/ 200/OB32 - 2298522

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Round cable set, for connection to Allen Bradley SLC 500, OB 32 and IB 32, with one 40-position socket strip and four 14-position socket strips, for splitting 32 channels into 4x8 channels, for OB 32, no. of positions 40/4x14, cable length 2.0 m

### Why buy this product

- System cable can be used to split 32 channels into 4 x 8 channels

### Key commercial data

Packing unit	1 pc
GTIN	 4 017918 612412
Weight per Piece (excluding packing)	405.4 g
Custom tariff number	85444290
Country of origin	Germany

### Technical data

#### General

Nominal voltage $U_N$	< 50 V AC
	60 V DC
Max. current carrying capacity per path	1 A
Max. conductor resistance	0.16 $\Omega$ /m
Length of cable	2 m
Single wire, cross section	0.14 mm <sup>2</sup>
AWG	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	7.8 mm
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4
Shielding	no

#### Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-1

## Cable - FLK 40/4X14/EZ-DR/ 200/OB32 - 2298522

### Technical data

#### Connector, module side

Number of positions	14
Connectors	IDC/FLK socket strip (2.54 mm)
Number of plugs	4

#### Connector, controller side

Number of positions	40
Connectors	IDC/FLK socket strip (2.54 mm)
Number of plugs	1

#### Supported controller

Control	ALLEN-BRADLEY SLC 500
- suitable I/O card	1746 OB 32
	1746 OV 32

### Classifications

#### eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

#### ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC000830

#### UNSPSC

UNSPSC 6.01	26121620
UNSPSC 7.0901	26121620
UNSPSC 11	26121620
UNSPSC 12.01	26121620
UNSPSC 13.2	26121620

### Approvals

#### Approvals

---

## Cable - FLK 40/4X14/EZ-DR/ 200/OB32 - 2298522

### Approvals

Approvals

GOST

---

Ex Approvals

---

Approvals submitted

---

### Approval details

GOST 

---