



datasheet for PL 2600 S W
 article number: 934158100



product description:	order number: 934 158-100
description:	Safety test lead with dual function safety test probe. Tip for penetration of insulation and oxide layers and 4 mm diameter pin for insertion into sockets. 4 mm diameter safety connector with right-angled outlet. Incl. Tip protection
typ:	PL 2600 S W schwarz/black
system:	4mm safety system
order number:	934 158-100
color	
other color versions:	
technical data	
measurement category	CAT II
norm	DIN EN 61010-031
pin dimensions	4mm
type of contact:	spring mounted pin
type of termination:	4mm diameter pin
cable type:	LEH-XY
cable specification:	high flexible lead
wire stranding:	259 x 0.07
rated voltage:	AC/DC 1000 V
rated current:	16 A
contact resistance:	20 mOhm
cable length:	100cm
conductor size:	1mm ²
cable material:	PVC
cable color:	black
material	
contact material:	copper beryllium
contact surface material:	nickel
housing material:	PA
environmental conditions:	
temperature range:	-15 °C to +70 °C
inflammable class:	
housing:	94 HB
cable:	94 HB

drawing

