

# Datasheet



## RS 811-7052

Splitter Box with:

- 3 x 32A 3P+N+E IEC 60309 Panel mount sockets
- 3 x 32A 3 pole MCB
- 3 Metre lead to 32A 3P+N+E IEC 60309 plug
- Black

Monitoring	N/A
Quantity Of Inputs	1
Voltage	400V
Amperage	32A
VA per Input (Load Capacity)	22kW
Frequency	50/60 Hz
Over Current Protection	3 x 3 Pole 32A MCB Breakers
Switch	No
Neon	No
Power Cable Wire Gauge	6.0mm <sup>2</sup> H07RN-F
Power Cable Length-Plug Attached	3M
Plug Type	IEC60309 Plug, 32A, 400V
Receptacle/Socket Type #1	IEC60309 Socket, 32A 400V
Style #1	Individual
Maximum Output per Receptacle/Socket #1	32A
Voltage per Receptacle/Socket #1	400V
Heavy Steel - Black Powder Coat	Yes
Configuration	Vertical Mount
Flush Mount	Yes
Product Warranty	Lifetime
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	Complies with EN 60950
Chassis Dimensions (HxWxD)	100mm x 332mm x 245mm