

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD


C

REV / 0L20-0042-96

07JAN97

ME

TM



500	LOOSE PIECE	323069
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMMAX RECOMMENDED OPERATING
TEMPERATURE:
343°C [650°F]THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.DWN
L OLMEDA 100CT94CHK
M ELLIS 100CT94APVD
S BORTNER 100CT94

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

AMP Incorporated
Harrisburg, PA 17105-3608NAME
TERMINAL, RING TONGUE,
STRATO-THERM™, DIAMOND GRIP™,
WIRE SIZE, 12-10 AWGSIZE
A3CAGE CODE
00779DRAWING NO
C-323069SCALE
4:1SHEET
1 OF 1REV
CFOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142


VOLTAGE RATING:

-

-

CIRCULAR MIL AREA:
2.62mm²-6.64mm² [5180-13100]

STRANDED WIRE

DIMENSIONS:
mm [in]MATERIAL
BODY, CU PER ASTM B152
SLEEVE, NI SIL PER
ASTM B122TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [1.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-FINISH
BODY, NP, QQ-N-290