









NOTE.

1. APPLICABLE ASS'Y CONNECTOR FOR JPT&MQS 81Pos.; P/N: 368190-1


 TE TREAD MARK.

 CAVITY MARK

 DATE CODE.

 RECYCLE MARKING.

⑤	BLACK	PP-M30	COVER HSG (CHINA ONLY)	9-368333-1
	BLACK	PP-M30	COVER HSG	368333-1
	COLOR	MATEIAL	DESCRIPTION	PART NO.

		DWN DR G00		 TE Connectivity	
		CHK YM CHOI			
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME COVER HSG FOR JPT&MQS ASS'Y 81Pas. ('B' TYPE)	
 3rd ANGLE PROJECTION		0 <XX<10 ± 0.2 10<XX<30 ± 0.25 30<XX ± 0.3 ANGLES ± 3°			
		APVD JK SONG			
		PRODUCT SPEC -----			
		APPLICATION SPEC -----		SIZE A3	
MATERIAL SEE TABLE		FINISH SEE TABLE		CAGE CODE 00779	
		WEIGHT ---		DRAWING NO C- 3 6 8 3 3 3	
CUSTOMER DRAWING				SCALE 1 : 1 SHEET 1 OF 1 REV B1	