

EK EKHA 130 T



Sample photo

Order symbol: EKHA 130 T
Product nbr: 2538101
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074013712
EI. number:
 Finland: 3425450
 Italy: 7502010
 Sweden: 2538101
 Norway:

Including: Flanged Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		190	190	130	Ingress Protection (EN 60529): IP 66/67
inch:		7.5	7.5	5.1	Impact Resistance (EN 62262): IK 08
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		Clear transparent			
Cover screws material:		Polyamide			
Cover screws colour:		Grey			
Gasket material:		Polyurethane			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
EKHA		Base, PC			
EKHS		Base, PC			
EKH 30-G		Cover			
EKH 80-G		Cover			
EKH 30-T		Cover			
EKH 80-T		Cover			
EKHVT		Mounting plate			
EKHXT		Mounting plate Pertinax			
EKV 12		DIN-35 Mounting rail			
					Certificates:
					Germanischer Lloyd (GL)
					Underwriters Laboratories
					Det Norske Veritas
					Bureau Veritas
					Fimko
					Lloyds Register of Shipping (LR)
					Europe EN 62208: 2003
					UL Canada
					Gost R

