



## HANDY-MATE

A lightweight yet rugged torpedo level, featuring an adjustable horizontal vial.

### HANDY-MATE SPECIFICATION

- Lightweight structural foamed polystyrene body.
- One adjustable horizontal block vial and one fixed plumb block vial.
- Accuracy +/- 1.0mm/m = 0.057° in standard position.
- Individual hanging packs, 5 per box.

### PRODUCT CODES

#### LENGTH

250mm/10"	L8-025
-----------	--------



## POCKET-MATE

A compact two vial torpedo level with a grooved base making it ideal for pipework.

### POCKET-MATE SPECIFICATION

- Tough ABS moulded body.
- One horizontal and one plumb vial.
- Accuracy +/- 1.0mm/m = 0.057° in standard position.
- Individual hanging packs, 5 per box.

### PRODUCT CODES

#### LENGTH

200mm/8"	L9-020
----------	--------



## PRO-MATE

A heavy duty torpedo level with a cast aluminium frame and magnetic base plate.

### PRO-MATE SPECIFICATION

- Tough aluminium frame with high visibility ABS centre.
- Magnetic base plate.
- Three vials: horizontal, vertical and 45°.
- Accuracy +/- 1.0mm/m = 0.057° in standard position.
- Top viewing window for the horizontal vial.
- Individual hanging cards, 5 per box.

### PRODUCT CODES

#### LENGTH

230mm/9"	L12-023
----------	---------