



414E C9000 QUICK ACTING COUPLER FEMALE BSP PARALLEL


maximum working pressure	bar 16	MPa 1,6	psi 232
working temperature	°C (Celsius) From -20 to 60	F (Fahrenheit) From -4 to 140	K (Kelvin) From 253 to 333
ball	stainless steel		
body	engineering grade polymer		
sub-base	nickel-plated brass		
'O'-rings	nitrile		
spring	stainless steel		



414E C9000 QUICK ACTING COUPLER FEMALE BSP PARALLEL

convert nominal diameter : mm | [inch](#)

convert flow rate : l/min | [cfm](#)

	DN (mm)	Flow Rate (l/min)	C	Pack Qty	Qty for Quotation
9414E07 13	7,2	2000	G1/4	6	<input type="text"/>
9414E07 17	7,2	2000	G3/8	6	<input type="text"/>
9414E07 21	7,2	2000	G1/2	6	<input type="text"/>