



ENGLISH

Datasheet

2 Output Toroidal Transformer, 50VA, 12 V ac

RS Stock number [540-5220](#)



Description:

Open Form Toroidal Transformers, 115-230Vac Primary, 30VA & 50VA

- Small size and low weight compared with traditional stacked laminated transformers
- Both primary and secondary windings may be connected in series or parallel
- Low induced noise (hum)
- Low level of radiated magnetic field
- Flexible lead outs, for ease of installation
- 100% electrical and flash testing

Specifications:

Rating:	50VA
Output (V):	12 + 12
Diameter:	80mm
Dimensions:	80 Dia. x 34mm
Height:	34mm
Number of Outputs:	2
Power Rating:	50VA
Primary Voltage Rating:	115 V ac, 230 V ac
Secondary Current:	2.08A
Secondary Voltage Rating:	12 V ac
Weight:	0.76kg
Centre Bolt:	M6
Typical Regulation (%):	13

