



ENGLISH

Datasheet

Stock No: 413-9023

RS Pro Polyether PUR 10m Long transparent Flexible Ducting Reinforced, 63mm Bend Radius



Product Details

Non-toxic Flexible Ducting

RS Pro polyurethane (PU) polyether hose with a PVC spiral. Can be used for suction, the transport of abrasive materials and dry foods.

White PVC helix in a clear non-toxic polyether polyurethane

Convoluted cover

High abrasion resistance

Also suitable for wet applications such as pharmaceutical preparation, fish transfer or leaf and grass collection

Temperature range -25 to +85°C

Note

All data refers to performance at 18°C. Any changes in temperature will affect the performance data



Specifications

Inner Diameter	63mm
Outer Diameter	71.5mm
Material	Polyether PUR
Length	10m
Suitable Applications	Abrasive Material, Agriculture, Cereal, Gardening, Grain, Organic Material, Powder, Scrap Processing, Suction
Colour	Transparent
Bend Radius	63mm
Reinforced	Yes