





F
E
D
C
B
A




GENERAL TOLERANCES

10 UNDER	±0.2
10 OVER 30 UNDER	±0.25
30 OVER	±0.3
ANGLE	±5°


				公差 (Tolerances)		所要数		DRWG. <i>G. Amano '97.7.77</i>	
				.000 → ±0.005 .00 → ±0.05		(R) (q)		DSN'D <i>MEMORANDUM '98.7.7</i>	
				.0 → ±0.1 . → ±0.3				CHK'D <i>K. S. Chino</i>	
				材料 (MAT'L)				APP'D	
D <i>Qty: 167 数量 ECN NO. 1486</i>				NYLON 66, 94V-2		MOLEX-JAPAN CO., LTD. 日本モレックス株式会社			
C <i>REMOVED 'X' ECN NO. 740</i>				熱処理 (H.T.)					
B ₁ <i>ロッキン 7-17</i>				HRc					
B <i>リブ: サークット NO.</i>				仕上げ (Finish)					
A <i>REVISED</i>						No. SD-5025-06R1		REV. D	
O <i>PROPOSED</i>									
記号 (LTR)		変更内容 (Rev.)		Date		Name		Scale 2/1	
								名称 (Name) MINI. FIT CONN. 6POS. RECEPTACLE HSG.	

F




E


D



C



B



A

一般公差	
10 未満	±0.2
10以上30未満	±0.25
30 以上	±0.3
角 度	±3°

				公差 (Tolerances)	所要数 (Req)	DRWG. <i>Y. Amano</i> '9/7 '77
				.000 → ±0.005 .00 → ±0.05		DSN'D <i>M. ENOMOTO</i> '9/9/77
				.0 → ±0.1 . → ±0.3		CHK'D <i>W. M.</i>
				材料 (MAT'L)	* MOLEX-JAPAN CO., LTD. 日本モレックス株式会社	APP'D <i>W. M.</i>
D	ロッキング支柱 ECN. NO. 1486	11/21/79	K.H.	NYLON 66, 94V-2		
C	REMOVED "X" ECN NO. 748	3/18/78	<i>W. M.</i>	熱処理 (H.T.)		
B ₁	ロッキングレブ	3/13/78	<i>W. M.</i>	HRc #		
B	リブ. サークット NO.	12/13/77	<i>W. M.</i>	仕上げ (Finish)		
A	REVISED	11/15/77	<i>W. M.</i>		No.	SD-5025-06R1
O	PROPOSED	9/7/77	<i>W. M.</i>	Scale 2/1	名称 (Name)	MINI. FIT CONN. 6POS. RECEPTACLE HSG.
記号 (LTR)	変更内容 (Rev.)	Date	Name	REV. <i>D</i>		