

LED LENSER® i7-DR

The LED Lenser i7-DR is a high-strength rechargeable torch for professional applications. Tough and compact it will fit the hand, pocket or case of any engineer. It features a single-hand Speed Focus with Fast Lock plus Advanced Focus System optics to keep the light consistent from flood to spot beam with an impressive range up to 180 metres. There is a choice of Power (220 lumens) or Low Power (25 lumens) light settings, providing everything from high-intensity illumination down to a softer light useful for reading maps or viewing diagrams. Either function is easily found thanks to a sensibly-located Dynamic Switch on the end of the barrel. A generous run time of 4 hours (Power) or 30 hours (Low Power) makes the i7-DR a dependable light instrument in the most demanding environments. It is supplied with a handy double charging base, enabling heavy users to have one battery in the torch while another one is being charged ready for use - all with energy-saving efficiency.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Compact rechargeable hand torch for everyday professional use
- CREE® Power LED Light Chip
- State-of-the-art, reliable German engineering
- Advanced Focus System (AFS). Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Speed Focus® with Fast Lock
- Dynamic Switch
- Power and Low Power light modes
- Additional extra battery unit
- Double charging base with charging indicator USB connection
- Water-resistant (IPX4)
- Detachable roll protection ring included

Technical Information	Power	Low Power
Lumens	220	25
Beam Distance (meters)	180	60
Run Time (hours)	4	30
Size:	130x36.5mm Ø	
Weight:	175g	
Batteries:	8 x NiMH	

Supplied with: Additional battery unit, Double Charging Base, USB cable, Roll Protection Ring, Wrist-Strap, Pouch, Rechargeable battery set (8 x AAA NiMH)

Code	Description	Unit Colour	Packaging	Barcode
5507DR	i7-DR	Black	Box	4029113550734

RRP ex.vat £58.29 / incl.vat £69.95

* Also compatible with AAA Alkaline batteries (not supplied)