



Potentiometer 47k

Part no.
Article no.
Catalog No.

M22-R47K
229492
M22-R47KQ



Powering Business Worldwide™

Delivery programme

Basic function			Potentiometer
Single unit/Complete unit			Single unit
Description			3 separate screw connections, $P_{max} = 0.5 W$ Accuracy of resistance value: $\pm 10\%$ (linear)
Contact sequence			
Impedance	R	k Ω	47
Protection type			IP66
Front ring			Front ring: titanium
Connection to SmartWire-DT			no

Approvals

Product Standards
UL File No.
UL Category Control No.
CSA File No.
CSA Class No.
North America Certification
Degree of Protection

IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking
E29184
NKCR
012528
3211-03
UL listed, CSA certified
UL/CSA Type 3R, 4X, 12, 13

Technical data ETIM 5.0

Low-voltage industrial components (EG000017) / Potentiometer for control circuit devices (EC001027)
Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Potentiometer for command devices
(ecl@ss8-27-37-12-27 [AKFD45010])

Resistance		Ohm	47000
Power consumption		W	0.5
Hole diameter		mm	22
Degree of protection (IP)			IP66

Dimensions



