

F51w/840 T8 Eco

0001611

Range features



CE

PRODUCT OVERVIEW

Light colour	840 Cool White
Technology	Fluorescent
Ordering number	0001611
Energy class	A
Lamp shape	Tubular
Lamp finish	Coated
Dimmable	Yes
Cap/Base	G13
Type	T8 Eco
EAN code	5410288016115
CRI (Ra)	85
Colour temperature (K)	4000
Luminous flux (Rated) (lm)	4400
Efficacy (Rated) 100h (lm/W)	86
Watt (Nominal) (W)	51
Voltage (V)	96

F51w/840 T8 Eco

0001611

DATA TABLE

General data

Ordering number	0001611
Technology	Fluorescent
Energy class	A
Average life (Nominal) (h)	15000
Lamp shape	Tubular
Lamp finish	Coated
Dimmable	Yes
Cap/Base	G13
Type	T8 Eco
EAN code	5410288016115
E-number FI	4940251
Product name	F51w/840 T8 Eco
Lamp mercury content (mg)	2.8
Control gear required	Yes
Fixture rating	Open
IEC Reference	IEC 60081
IEC Reference 2	IEC 61195
Intended purpose	General lighting
Special purpose lamp	No
Sales pack quantity	25
Rated survival factor at 2000 h 50Hz	0.99
Rated survival factor at 4000 h 50Hz	0.98
Rated survival factor at 6000 h 50Hz	0.96
Rated survival factor at 8000 h 50Hz	0.93
Rated survival factor at 12000 h 50Hz	0.92
Rated survival factor at 16000 h 50Hz	0.8
Rated survival factor at 20000 h 50Hz	0.5

F51w/840 T8 Eco

0001611

Optical data

Light colour	840 Cool White
CRI (Ra)	85
Colour temperature (K)	4000
Luminous flux (Rated) (lm)	4400
Luminous flux (Nominal) (lm)	4400
Ambient temperature for maximum luminous flux (°C)	25
Rated lumen maint. factor at 2000 h 50Hz	0.96
Rated lumen maint. factor at 4000 h 50Hz	0.94
Rated lumen maint. factor at 6000 h 50Hz	0.92
Rated lumen maint. factor at 8000 h 50Hz	0.91
Rated lumen maint. factor at 12000 h 50Hz	0.9
Rated lumen maint. factor at 16000 h 50Hz	0.89
Rated lumen maint. factor at 20000 h 50Hz	0.87

Electrical data

kWh per 1000 hours burning time	60
Efficacy (Rated) 100h (lm/W)	86
Watt (Nominal) (W)	51
Watt (Rated) (W)	51
Voltage (V)	96


Physical data

Weight (kg)	0.20
Length base to base (mm) - A	1500
Length base to pin Min-Max - B	1504.7-1507.1
Max overall length (mm)	1514.2
Lamp Diameter (mm) - D	26
Single package dimensions (L x W x H)	151.10 x 2.90 x 2.80
Single package volume (dm3)	1.227
Single product net weight (kg)	0.20
Single product gross weight (kg)	0.23
Single packaging weight (kg)	0.03
Outer package dimensions (L x W x H)	154.50 x 15.50 x 15.00
Outer package net weight (kg)	5.00
Outer package gross weight (kg)	6.07
Outer package volume (dm3)	35.921
Outer packaging weight (kg)	1.07
Units per outer package	25

F51w/840 T8 Eco

0001611

TECHNICAL DRAWINGS



ENERGY LABEL

