

HARTING Ltd | Caswell Road | Brackmills Industrial Estate | Northampton | NN4 7PW  
 Phone +44 1604 827500 | Fax +44 1604 706777



INVESTOR IN PEOPLE



Reg. No. 002204 QM



## Han-Yellock® Kit

### Part Number – [6630 297 0002 00](#)

The above part number refers to a kit of parts for the HARTING Han – Yellock® Size 30 range.

This kit consist of the following parts.

Part Number	Description	Qty per Kit
1112 300 1501	Han - Yellock® side entry Hood M25	1
1112 300 0110	Han - Yellock® Hood Carrier with grooved lock button	1
1112 300 0301	Han - Yellock® Bulkhead housing	1
1105 105 3001	Han - Yellock® Crimp module / insert	6
1105 001 2601	Han - Yellock® Quick Lock ground contact	2
1199 000 0001	Han - Yellock® Module / insert removal tool	1

You will need to choose the correct crimp contacts to suit the wire gauges you are using and the type of contact multiplier for your particular application.

#### Crimp contact sizes.

1105 000 6101	0.14 – 0.37 mm <sup>2</sup>
1105 000 6102	0.5 mm <sup>2</sup>
1105 000 6103	0.75 mm <sup>2</sup>
1105 000 6104	1.0 mm <sup>2</sup>
1105 000 6105	1.5 mm <sup>2</sup>
1105 000 6106	2.5 mm <sup>2</sup>
1105 000 6107	3.0 mm <sup>2</sup>
1105 000 6108	4.0 mm <sup>2</sup>

#### Han – Yellock® multipliers.

	Bus bar contacts	Single contacts	Circuit diagram
1105 105 2801	0	5	
1105 105 2802	2	3	
1105 105 2803	3	2	
1105 105 2804	4	1	
1105 105 2805	5	0	