





2		1				
LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			L3	REVISED PER ECO-11-004587	11MAR11	RK HMR



- 1 INSULATION DIA .135 MAX
- 2 FITS TAB .020 THK
- 3 SUPERSEDED BY 8-640917-1

3	50	LOOSE PC,BAG	8-640917-5
	100	LOOSE PC,BOX	8-640917-1
	-	TAPE MOUNTED	640917-2
	-	LOOSE PIECE	640917-1
	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEM		MAX RECOMMENDED OPERATING TEMPERATURE: 105° C MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L OLMEDA 26JUN95	 TE Connectivity							
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 300V MAX	DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -	CHK M ELLIS 26JUN95	NAME RECEPTACLE, 187 SERIES, FASTON™, PIDG™, WIRE SIZE: 22-18 AWG							
	FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111								APVD B BARE 26JUN95		
FOR ORDER ENTRY		1-800-526-5142	CIRCULAR MIL AREA: 0.26-0.96mm² [509-1900] STRANDED	MATERIAL BODY, BRASS .016 SLV, NYLON, COLOR:RED		FINISH BODY, TIN	PRODUCT SPEC —	APPLICATION SPEC —	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-640917	RESTRICTED TO —
		CUSTOMER DRAWING					SCALE NTS	SHEET 1 OF 1	REV L3				