

Electromagnetic ballasts



Type: L7/9/11.411 240V/50HZ

Item number: 164335

Standard version

Vacuum-impregnated with polyester resin

Lamp type:	TC-S
Output [W]:	0009
Voltage [V]:	240
Shape [mm*mm]:	28X41
Stack length [mm]:	034
Fixing centre [mm]:	075
Overall length [mm]:	085
Protection from overheating:	Without thermal cut-out
Encapsulated:	No
Delta t Max. [K]:	60
Connection:	Push-in/IDC terminal
Earth terminal:	No
Frequency [Hz]:	50
Protection class:	Class of protection I



For a large drawing of **item 164335** please click on the thumbnail-

Unit: 10 pcs.

tw 130
EN 61347 (Safety)
EN 60921 (Working method)



