

Polycarbonate enclosures PK



PK accessories Page 31 System accessories Page 537 Polyamide cable gland Page 709

Material:

- Housing of fibre-glass reinforced polyamide
- Cover either transparent (version .100) or grey (version .000), made from fibre-glass-reinforced polycarbonate
- Cover screws from polyamide
- Insulating bung from polyethylene
- All-round foamed-in PU seal

Colour:

RAL 7035

Protection category:

IP 66 to IEC 60 529

Supply includes:

- Enclosure with cover
- Cover screws
- Insulating bungs for wall mounting screws

Approvals:

- UL
- Bureau Veritas

Detailed drawings:

Available on the Internet.

Width mm		65	94	94	94	110	110	Page
Height mm		65	65	94	94	110	110	
Depth mm		57	57	57	81	66	90	
Model No. PK		9500.000	9502.000	9504.000	9505.000	9506.000	9507.000	
	Packs of	12	8	6	6	6	6	
Cover	Transparent							
	Grey							

Accessories

Support rail	Installation in the width	12	–	–	9564.000	9564.000	9564.000	9564.000	31
TS 35/7.5	Installation in the height	12	–	–	9564.000	9564.000	9564.000	9564.000	31
Wall mounting brackets		40	9583.000	9583.000	9583.000	9583.000	9583.000	9583.000	31
Turn-lock fastener		100	9582.000	9582.000	9582.000	9582.000	9582.000	9582.000	31
Hinges		10 sets	9580.000	9580.000	9580.000	9580.000	9580.000	9580.000	31

Width mm		130	130	130	130	130	130	Page
Height mm		94	94	94	94	130	130	
Depth mm		57	57	81	81	75	75	
Model No. PK		9508.100	9508.000	9509.100	9509.000	9510.100	9510.000	
	Packs of	4	4	4	4	4	4	
Cover	Transparent							
	Grey							

Accessories

Mounting plate			–	–	–	–	9545.000	9545.000	31
	Packs of		–	–	–	–	10	10	
Support rail	Installation in the width	12	9565.000	9565.000	9565.000	9565.000	9565.000	9565.000	31
TS 35/7.5	Installation in the height	12	9564.000	9564.000	9564.000	9564.000	9565.000	9565.000	31
Wall mounting brackets		40	9583.000	9583.000	9583.000	9583.000	9583.000	9583.000	31
Turn-lock fastener		100	9582.000	9582.000	9582.000	9582.000	9582.000	9582.000	31
Hinges		10 sets	9580.000	9580.000	9580.000	9580.000	9580.000	9580.000	31

Polycarbonate enclosures PK

Width mm		130	130	180	180	180	180	Page
Height mm		130	130	94	94	94	94	
Depth mm		99	99	57	57	81	81	
Model No. PK		9511.100	9511.000	9512.100	9512.000	9513.100	9513.000	
	Packs of	4	4	2	2	2	2	
Cover	Transparent	■	—	■	—	■	—	
	Grey	—	■	—	■	—	■	

Accessories

Mounting plate		9545.000	9545.000	—	—	—	—	31
	Packs of	10	10	—	—	—	—	
Support rail TS 35/7.5	Installation in the width	12	9565.000	9565.000	9566.000	9566.000	9566.000	31
	Installation in the height	12	9565.000	9565.000	9564.000	9564.000	9564.000	31
Wall mounting brackets	40	9583.000	9583.000	9583.000	9583.000	9583.000	9583.000	31
Turn-lock fastener	100	9582.000	9582.000	9582.000	9582.000	9582.000	9582.000	31
Hinges	10 sets	9580.000	9580.000	9580.000	9580.000	9580.000	9580.000	31

Width mm		180	180	180	180	180	180	Page
Height mm		110	110	110	110	110	110	
Depth mm		90	90	111	111	165	165	
Model No. PK		9514.100	9514.000	9515.100	9515.000	9516.100	9516.000	
	Packs of	2	2	2	2	2	2	
Cover	Transparent	■	—	■	—	■	■	
	Grey	—	■	—	■	—	—	

Accessories

Mounting plate		9547.000	9547.000	9547.000	9547.000	9547.000	9547.000	31
	Packs of	10	10	10	10	10	10	
Support rail TS 35/7.5	Installation in the width	12	9566.000	9566.000	9566.000	9566.000	9566.000	31
	Installation in the height	12	9564.000	9564.000	9564.000	9564.000	9564.000	31
Wall mounting brackets	40	9583.000	9583.000	9583.000	9583.000	9583.000	9583.000	31
Turn-lock fastener	100	9582.000	9582.000	9582.000	9582.000	9582.000	9582.000	31
Hinges	10 sets	9581.000	9581.000	9581.000	9581.000	9581.000	9581.000	31

Width mm		182	182	182	182	182	182	254	254	Page
Height mm		180	180	180	180	180	180	180	180	
Depth mm		90	90	111	111	165	165	90	90	
Model No. PK		9517.100	9517.000	9518.100	9518.000	9519.100	9519.000	9520.100	9520.000	
	Packs of	1	1	1	1	1	1	1	1	
Cover	Transparent	■	—	■	—	■	—	■	—	
	Grey	—	■	—	■	—	■	—	■	

Accessories

Mounting plate		9548.000	9548.000	9548.000	9548.000	9548.000	9548.000	9549.000	9549.000	31
	Packs of	10	10	10	10	10	10	8	8	
Support rail TS 35/7.5	Installation in the width	12	9566.000	9566.000	9566.000	9566.000	9566.000	9567.000	9567.000	31
	Installation in the height	12	9566.000	9566.000	9566.000	9566.000	9566.000	9566.000	9566.000	31
Wall mounting brackets	40	9583.000	9583.000	9583.000	9583.000	9583.000	9583.000	9583.000	9583.000	31
Turn-lock fastener	100	9582.000	9582.000	9582.000	9582.000	9582.000	9582.000	9582.000	9582.000	31
Hinges	10 sets	9581.000	9581.000	9581.000	9581.000	9581.000	9581.000	9581.000	9581.000	31

Width mm		254	254	254	254	360	360	360	360	Page
Height mm		180	180	180	180	254	254	254	254	
Depth mm		111	111	165	165	111	111	165	165	
Model No. PK		9521.100	9521.000	9522.100	9522.000	9523.100	9523.000	9524.100	9524.000	
	Packs of	1	1	1	1	1	1	1	1	
Cover	Transparent	■	—	■	—	■	—	■	—	
	Grey	—	■	—	■	—	■	—	■	

Accessories

Mounting plate		9549.000	9549.000	9549.000	9549.000	9550.000	9550.000	9550.000	9550.000	31
	Packs of	8	8	8	8	4	4	4	4	
Support rail TS 35/7.5	Installation in the width	12	9567.000	9567.000	9567.000	9568.000	9568.000	9568.000	9568.000	31
	Installation in the height	12	9566.000	9566.000	9566.000	9567.000	9567.000	9567.000	9567.000	31
Wall mounting brackets	40	9583.000	9583.000	9583.000	9583.000	9583.000	9583.000	9583.000	9583.000	31
Turn-lock fastener	100	9582.000	9582.000	9582.000	9582.000	9582.000	9582.000	9582.000	9582.000	31
Hinges	10 sets	9581.000	9581.000	9581.000	9581.000	9581.000	9581.000	9581.000	9581.000	31