


**OMNIMATE Signal - series BL/SL 3.50**  
**BL 3.50/06/90 SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
[www.weidmueller.com](http://www.weidmueller.com)



Female connectors with clamping yoke screw system for connecting conductors at 3.50 mm pitch. They provide space for labelling and can be coded.

**General ordering data**

|              |                                                                                                                                                   |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------------------|
| Type         | BL 3.50/06/90 SN OR BX                                                                                                                            |
| Order No.    | <a href="#">1638590000</a>                                                                                                                        |
| Version      | PCB plug-in connector, female plug, 3.50 mm, No. of poles: 6, 90°, Clamping yoke connection, Clamping range, rated connection, max.: 1.5 mm², Box |
| GTIN (EAN)   | 4008190276133                                                                                                                                     |
| Qty.         | 84 pc(s).                                                                                                                                         |
| Product data | IEC: 320 V / 12 A / 0.2 - 1.5 mm²<br>UL: 300 V / 8 A / AWG 28 - AWG 14                                                                            |
| Packaging    | Box                                                                                                                                               |

## OMNIMATE Signal - series BL/SL 3.50

### BL 3.50/06/90 SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |         |
|------------|---------|
| Net weight | 3.702 g |
|------------|---------|

### System parameters

|                                              |                                     |                                            |                     |
|----------------------------------------------|-------------------------------------|--------------------------------------------|---------------------|
| Product family                               | OMNIMATE Signal - series BL/SL 3.50 | Type of connection                         | Field connection    |
| Wire connection method                       | Clamping yoke connection            | Pitch in mm (P)                            | 3.5 mm              |
| Pitch in inches (P)                          | 0.138 inch                          | Conductor outlet direction                 | 90°                 |
| No. of poles                                 | 6                                   | L1 in mm                                   | 17.5 mm             |
| L1 in inches                                 | 0.689 inch                          | Number of rows                             | 1                   |
| Pin series quantity                          | 1                                   | Rated cross-section                        | 1.5 mm <sup>2</sup> |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch              | Touch-safe protection acc. to DIN VDE 0470 | IP 20               |
| Can be coded                                 | Yes                                 | Stripping length                           | 6 mm                |
| Tightening torque, min.                      | 0.2 Nm                              | Tightening torque, max.                    | 0.25 Nm             |
| Clamping screw                               | M 2                                 | Screwdriver blade                          | 0.4 x 2.5           |
| Screwdriver blade standard                   | DIN 5264                            | Plugging cycles                            | 25                  |
| push-in force/pole                           | 10 N                                | Withdrawal force per pole                  | 4 N                 |
| Packaging                                    | Box                                 |                                            |                     |

### Material data

|                                       |          |                                       |                          |
|---------------------------------------|----------|---------------------------------------|--------------------------|
| Insulating material                   | PBT      | Colour                                | Orange                   |
| Colour chart (similar)                | RAL 2000 | Insulating material group             | IIIa                     |
| CTI                                   | ≥ 200    | Insulation resistance                 | ≥ 10 <sup>8</sup> Ω      |
| UL 94 flammability rating             | V-0      | Contact material                      | Cu-Leg                   |
| Contact surface                       | tinned   | Layer structure of plug contact       | 4-8 µm Sn hot-dip tinned |
| Storage temperature, min.             | -25 °C   | Storage temperature, max.             | 55 °C                    |
| Max. relative humidity during storage | 80 %     | Operating temperature, min.           | -50 °C                   |
| Operating temperature, max.           | 100 °C   | Temperature range, installation, min. | -30 °C                   |
| Temperature range, installation, max. | 100 °C   |                                       |                          |

### Conductors suitable for connection

|                                                 |                      |                                                 |                     |
|-------------------------------------------------|----------------------|-------------------------------------------------|---------------------|
| Clamping range, rated connection, min.          | 0.08 mm <sup>2</sup> | Clamping range, rated connection, max.          | 1.5 mm <sup>2</sup> |
| Wire connection cross section AWG, min.         | AWG 28               | Wire connection cross section AWG, max.         | AWG 14              |
| Solid, min. H05(07) V-U                         | 0.2 mm <sup>2</sup>  | Solid, max. H05(07) V-U                         | 1.5 mm <sup>2</sup> |
| Flexible, min. H05(07) V-K                      | 0.2 mm <sup>2</sup>  | Flexible, max. H05(07) V-K                      | 1.5 mm <sup>2</sup> |
| w. plastic collar ferrule, DIN 46228 pt 4, min. | 0.2 mm <sup>2</sup>  | w. plastic collar ferrule, DIN 46228 pt 4, max. | 1.5 mm <sup>2</sup> |
| w. wire end ferrule, DIN 46228 pt 1, min.       | 0.2 mm <sup>2</sup>  | w. wire end ferrule, DIN 46228 pt 1, max.       | 1.5 mm <sup>2</sup> |
| Plug gauge acc. to EN 60999 a x b; Ø            | 2.4 mm x 1.5 mm      |                                                 |                     |

**OMNIMATE Signal - series BL/SL 3.50**  
**BL 3.50/06/90 SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Technical data**
**Rated data acc. to IEC**

|                                                                           |                        |                                                                       |                   |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|-------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. no. of poles (Ta = 20°C)                          | 12 A              |
| Rated current, max. no. of poles (Ta = 20°C)                              | 10 A                   | Rated current, min. no. of poles (Ta = 40°C)                          | 10 A              |
| Rated current, max. no. of poles (Ta = 40°C)                              | 8 A                    | Rated voltage for surge voltage class / pollution degree II/2         | 320 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 160 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV                 | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV            |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV                 | Short-time withstand current resistance                               | 3 x 1s with 100 A |

**Rated data acc. to CSA**

|                               |                                                                                   |                               |                |
|-------------------------------|-----------------------------------------------------------------------------------|-------------------------------|----------------|
| Institute (CSA)               |  | Certificate No. (CSA)         | 154685-1318353 |
| Rated voltage (Use group B)   | 300 V                                                                             | Rated voltage (use group D)   | 300 V          |
| Rated current (use group B)   | 10 A                                                                              | Rated current (use group D)   | 10 A           |
| Wire cross-section, AWG, min. | AWG 28                                                                            | Wire cross-section, AWG, max. | AWG 14         |
| Reference to approval values  | Specifications are maximum values, details - see approval certificate.            |                               |                |

**Rated data acc. to UL 1059**

|                               |                                                                                     |                               |        |
|-------------------------------|-------------------------------------------------------------------------------------|-------------------------------|--------|
| Institute (UR)                |  | Certificate No. (UR)          | E60693 |
| Rated voltage (use group B)   | 300 V                                                                               | Rated voltage (use group D)   | 300 V  |
| Rated current (use group B)   | 8 A                                                                                 | Rated current (use group D)   | 8 A    |
| Wire cross-section, AWG, min. | AWG 28                                                                              | Wire cross-section, AWG, max. | AWG 14 |
| Reference to approval values  | Specifications are maximum values, details - see approval certificate.              |                               |        |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001284    | ETIM 4.0   | EC002637    |
| ETIM 5.0   | EC002637    | ETIM 6.0   | EC002637    |
| UNSPSC     | 30-21-18-10 | eClass 5.1 | 27-26-07-04 |
| eClass 6.2 | 27-26-07-04 | eClass 7.1 | 27-44-04-02 |
| eClass 8.1 | 27-44-04-02 | eClass 9.0 | 27-44-04-02 |
| eClass 9.1 | 27-44-04-02 |            |             |

## OMNIMATE Signal - series BL/SL 3.50 BL 3.50/06/90 SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Notes

Notes

- Additional colours on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- Max. outer diameter of the conductor: 2.9 mm
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

IPC conformity

The products are developed, manufactured and delivered according to the internationally recognised IPC-A-610 standard, category "permissible". More extensive demands on the products can be evaluated on request.

### Approvals

Approvals



ROHS

Conform

### Downloads




Safety notice

[Safety indication](#)

## OMNIMATE Signal - series BL/SL 3.50 BL 3.50/06/90 SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



## OMNIMATE Signal - series BL/SL 3.50 BL 3.50/06/90 SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
www.weidmueller.com

## Accessories

### Coding elements



**Only connects what is supposed to be connected:  
the right connection at the right place.**

Coding elements and locking devices clearly assign connecting elements during the manufacturing process and operation

The coding elements and locking devices are inserted prior to assembly or during the cable assembly phase. The Weidmüller alternative: configure online using the variant configurator to precode prior to delivery.

Incorrect assembly on the circuit board and incorrect plugging of connecting elements is no longer possible. The advantage: no troubleshooting during manufacture and no operational errors by the user.

### General ordering data

| Type               | Order No.                  | Version                                                                              | GTIN (EAN)    | Qty.       | Product data | Packaging |
|--------------------|----------------------------|--------------------------------------------------------------------------------------|---------------|------------|--------------|-----------|
| BL SL 3.5 KO<br>OR | <a href="#">1693430000</a> | PCB plug-in connector,<br>Accessories, Coding<br>element, Orange, No. of<br>poles: 1 | 4008190867447 | 100 pc(s). |              | Box       |
| BL SL 3.5 KO<br>SW | <a href="#">1610100000</a> | PCB plug-in connector,<br>Accessories, Coding<br>element, Black, No. of<br>poles: 1  | 4008190187637 | 100 pc(s). |              | Box       |

# Addresses worldwide

Let's connect.

**AE United Arab Emirates**  
Weidmüller Middle East FZE  
Warehouse Q3-79  
SAIF-Zone  
P.O. BOX 8591  
Sharjah  
Telephone number +971 65572723  
Fax number +971 65572724  
wme.info@weidmuller.com

**AF Afghanistan**  
Representative Office  
  
AF 11050 Beograd  
Telephone number +381 11 2885 274  
Fax number +381 11 2885 274  
zoran.rabrenovic@weidmuller.com

**AO Angola**  
Please contact  
Phambili Interface  
South Africa

**AR Argentina**  
CPI SA  
Bauness 2660  
C1431DOF Buenos Aires  
Telephone number +54 11 4523 8008  
Fax number +54 11 4522 0546  
info@cpi.com.ar  
www.cpi.com.ar

**AT Austria**  
Weidmüller GmbH  
IZ NOE Süd, Str 2b, Obj M59,  
2355 Wiener Neudorf  
Telephone number +43 2236 67080  
Fax number +43 2236 6708-899  
office.at@weidmuller.com  
www.weidmuller.com

**AU Australia**  
Weidmüller Pty. Ltd.  
PO BOX 6944  
Huntingwood 2148  
Huntingwood Drive 43  
Huntingwood NSW 2148  
Telephone number +61 2 9671 9999  
Fax number +61 2 9671 9911  
info@weidmuller.com.au  
www.weidmuller.com.au

**AZ Azerbaijan**  
Representative Office  
Weidmüller Interface  
Demirchi Tower, 4th floor  
37, Khojali ave.  
AZ 1025 Baku  
Telephone number +994 12 488 80 36  
Fax number +994 12 488 80 37  
aliyar.hashimli@weidmuller.com

**BA Bosnia and Herzegovina**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Serbia  
  
or  
BH ES Elektrosistem d.o.o.  
Palih boraca 104  
78000 Banja Luka  
Telephone number +387 51 420 340  
Fax number  
elistic@inecco.net

BIG electric d.o.o  
Mladena Stojanovića 117A  
78000 Banja Luka  
Telephone number +387 51926277  
Fax number +387 51926277  
bigelectric@blic.net  
www.bigelectric.ba

**BE Belgium**  
Weidmüller Benelux B. V.  
Mechelsesteenweg 519 bus  
6 en 7  
1930 Nossegem  
Telephone number +32 2 752 40 70  
Fax number +32 2 751 36 06  
info@weidmuller.be  
www.weidmuller.be

**BG Bulgaria**  
Weid-Bul EOOD  
Bul. "Kliment Ohridski" 13  
1756 Sofia  
Telephone number +359 2 963 2560  
Fax number +359 2 963 1098  
sofia@weidbul.com  
www.weidbul.com

**BH Bahrain**  
Khayber Trading Company  
P.O Box 1976  
Manama  
Telephone number +973 720747  
Fax number +973 720331  
khayber@batelco.com.bh

**BR Brazil**  
Weidmüller Conexel do Brasil  
Conexões Elétricas Ltda.  
Av. Presidente Juscelino, 642  
- Piraporinha  
Diadema, São Paulo  
09950-370  
Telephone number +55 (11) 4366-9600  
Fax number +55 (11) 4362-1677  
vendas@weidmuller.com.br  
www.weidmuller.com.br

**BW Botswana**  
Please contact  
Phambili Interface  
South Africa

**BY Belarus**  
TECHNIKON Ltd.  
Nezavisimosti pr. 177-9  
220125 Minsk  
Telephone number +375 17 393-11-77  
Fax number +375 17 3930080  
wm@technikon.by

**CA Canada**  
W Interconnections Canada Inc.  
10 Spy Court  
Markham Ontario L3R 5H6  
Telephone number +1 (905) 475-1507 Ext. 9836  
Fax number +1 (905) 475-2798  
support@weidmuller.ca  
www.weidmuller.ca

**CG Congo**  
Please contact  
Phambili Interface  
South Africa

**CH Switzerland**  
Weidmüller Schweiz AG  
Rundbuckstraße 2  
8212 Neuhausen am  
Rheinfall SH  
Telephone number +41 52 674 07 07  
Fax number +41 52 674 07 08  
info@weidmuller.ch  
www.weidmuller.ch

**CL Chile**  
CPI CHILE LTDA  
Av. Presidente Frei Montalva  
6001, 47 complejo el cortijo  
Santiago - Conchalí  
Telephone number +562 963 8440  
Fax number +562 963 8440  
cpi@cpichile.cl  
www.cpiichile.cl

**CN China**  
Weidmüller Interface  
(Shanghai) Co. Ltd.  
100 Yutong Road  
25 F. BM Intercontinental  
Business Center  
200070 Shanghai  
Telephone number +86 21-22195008  
Fax number +86 21-22195009  
customer.hotline@weidmuller.com.cn  
www.weidmuller.com.cn

**CO Colombia**  
Automatización Avanzada S. A.  
Carrera 97 No., 24 c - 23  
Bodega 4  
110911 Bogotá-D.C.  
Telephone number +57 (1) 547-8510  
Fax number +57 (1) 422-3044  
comercial@automatizacionavanzada.com  
www.automatizacionavanzada.com

**CR Costa Rica**  
ELVATRON S. A.  
la Uruca 400 Norte Banco  
Costa Rica  
San Jose Costa Rica  
Telephone number +506 2961-060  
Fax number +506 5200-609  
dirk.haase@elvatron.com  
www.elvatron.com

**CZ Czech Republic**  
Weidmüller s.r.o.  
Lomnického 5/1705  
140 00 Praha 4  
Telephone number +420 244 001 400  
Fax number +420 244 001 499  
office@weidmuller.cz  
www.weidmuller.cz

**DE Germany**  
Weidmüller GmbH & Co. KG  
Ohmstraße 9  
32758 Detmold  
Postfach 30 54  
32720 Detmold  
Telephone number +49 5231 1428-0  
Fax number +49 5231 14-292083  
weidmuller@weidmuller.de  
www.weidmuller.de

**DK Denmark**  
Weidmüller Danmark  
Vallensbækvej 18A  
2605 Brøndby  
Telephone number +45 27747800  
kundeservice@weidmuller.dk  
www.weidmuller.dk

**DZ Algeria**  
SARL INTER ELECTRIC  
1a Angles des Rues Okba Ibn  
Nafaa et Hassi Beida  
2300 Annaba  
Telephone number  
Fax number  
contact@inter-electric.com

**EC Ecuador**  
Elsystec S. A., Electricidad  
Sistemas y Tecnología  
Vasco de Contreras N35-251  
y Mañosca  
Quito - Pichincha  
Telephone number +593 22456510  
Fax number +593 22456755  
Elsystec@uio.satnet.net

**EE Estonia**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Latvia  
  
or  
SLO Eesti AS  
  
11415 Tallinn  
Telephone number +372 6 272 200  
Fax number  
info@slo.ee

SLO Eesti AS  
  
12618 Tallinn  
Telephone number +372 622 9119  
Fax number  
elit@elit.ee  
  
Soots Interface OÜ  
Pärnu mnt 142  
11317 Tallinn  
Telephone number +372 609 6933  
Fax number  
info@sootsinterface.ee  
www.sootsinterface.ee

**EG Egypt**  
Standard Electric (OMEGA)  
1, Abdelhamid Badawy Street  
Heliopolis  
Cairo  
Telephone number +202 21805111  
Fax number +202 21805600  
stdelec@rite.com

**ES Spain**  
Weidmüller, S. A.  
Narcis Monturiol 11-13, Pol.  
Ind. Sudoeste  
8960 Sant Just  
Desvern - Barcelona  
Telephone number +34 934 803 386  
Fax number +34 933 718 055  
weidmuller@weidmuller.es  
www.weidmuller.es

**FI Finland**  
Weidmüller Suomi,  
Weidmüller Aktiebolagetin  
sivuliike  
Koy Plaza Vivace  
Äyritie 8C  
FI 1510 Vantaa  
Telephone number +358 20 7351300  
Fax number +358 800 114 667  
asiakaspalvelu@weidmuller.fi  
www.weidmuller.fi

**FR France**  
Weidmüller E. U. R. L.  
2 Boulevard de l'Oise  
CS 31100 CERGY  
95095 CERGY PONTOISE  
Cedex  
Telephone number +33 1 34 24 55 00  
Fax number +33 1 34 24 55 01  
mail@weidmuller.fr

**GB Great Britain**  
Weidmüller Ltd.  
Klippon House  
Centurion Court Office Park,  
Meridian East, Meridian  
Business Park  
Leicester  
LE19 1TP  
Telephone number +44 116 282 3470  
Fax number +44 116 289 3582  
marketing@weidmuller.co.uk  
www.weidmuller.co.uk

**GE Georgia**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.

**GH Ghana**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
South Africa.

**GR Greece**  
G.A. Solutions  
Ippokratous 11 Metamorfosi  
144 52 Athen  
Telephone number +30 210 2823233  
Fax number +30 210 2823233  
info@weidmuller.gr  
www.weidmuller.gr

**GT Guatemala**  
Prestelectro, Prestegard  
Electro, S.A.  
Avenida Petapa 44-22,  
Zona 12  
Guatemala City  
Telephone number +502 2442-3346  
Fax number +502 2476-8945  
ventas@prestelectro.com

**HK Hong Kong**  
Weidmüller (Hong Kong)  
Limited Co. Ltd.  
Unit 1617, Metropolis Tower  
No. 10 Metropolis Drive,  
Hung Hom, Kowloon  
Telephone number +852 3154 8088  
Fax number +852 31548099  
Info-hk@weidmuller.com.hk

**HR Croatia**  
ElektroPARTNER d.o.o.  
Slavonska avenija 24/6  
HR-10000 Zagreb  
Telephone number +385 (1) 6184 793  
Fax number +385 (1) 6184 795  
elektropartner@zg.t-com.hr  
www.elektropartner.hr

**HU Hungary**  
Weidmüller Kereskedelmi Kft.  
Budapest  
Gubacsi út 6.  
1097  
Telephone number +36 1 382 7700  
Fax number +36 1 382 7701  
info@weidmuller.hu  
www.weidmuller.hu

**ID Indonesia**  
PT. Nego Electrindo  
Ruko Mega Grosir Cempaka  
Mas Blok I No. 20 - 22  
Jakarta 10640  
Telephone number +62 21 42882255  
Fax number +62 21 42882266  
sales@negoelectrindo.co.id

**IE Ireland**  
Please contact  
Weidmüller Ltd.  
Great Britain

**IL Israel**  
A. U. Shay Ltd.  
23/25, Embarr Street  
49222 Petach-Tikva  
P.O. Box 1 00 49  
49222 Petach-Tikva  
Telephone number +972 3-923-3601  
Fax number +972 3-923-4601  
shay@uriel-shay.com  
www.uriel-shay.com  
ATEKA Ltd.  
4, Ha Tavor lane Industrial  
area Segula  
49691 Petach-Tikva  
P.O. Box 4710  
Petach-Tikva  
Telephone number +972 73-200-1311  
Fax number +972 3-924 4245  
marketing@ateka.co.il  
www.ateka.co.il



You can find all Weidmüller addresses and your local contact on the internet at: [www.weidmuller.com/countries](http://www.weidmuller.com/countries)

Let's connect.

Sales company 

Representation abroad 

without representation abroad 

|                                                                                                                                                                                                                                                          |                                                                                                                                                                                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                       |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>IN</b> <b>India</b><br>Representative Office<br>Weidmüller Electronics India Pvt. Ltd.<br>No. 9, Union Street, Off. Infantry Road<br>BANGALORE<br>560 001<br>Telephone number +91-80-22860028<br>wmi@weidmuller.in<br>www.weidmuller.com              | <b>KW</b> <b>Kuwait</b><br>Kana Controls General Trading & Contracting Co. W. L. L.<br>Al Rai Industrial Area, Plot 28-30, St. 31<br>13016 Safat<br>B.P. 25593<br>Telephone number +965 4741373<br>Fax number +965 4741537<br>info@kanacontrols.com<br><br>Petroleum Services Co. W.L.L.<br>Kuwait Trade Free Zone Area P.O. Box 4098 Safat 13041<br><br>Telephone number +96524610801/2/3 ext. 208 II<br>Fax number +96524613754<br>psc-systems@petserv.net | <b>MD</b> <b>Moldova</b><br>Inoxpa Solutions SRL<br>20, Igor Vieru street<br>MD-2075 Chisinau<br>Moldova<br>Telephone number +373 (22) 866665<br>Fax number +373 (22) 866663<br>atiuleanu@gmp-moldova.com<br>www.gmp-moldova.com                                                             | <b>NA</b> <b>Namibia</b><br>Please contact<br>Phambili Interface<br>South Africa                                                                                                                                                                                                                                                                                                            | <b>PK</b> <b>Pakistan</b><br>Automation Controls (Pak) Apartment No. 33 C III, Chensab Block, Allama Iqbal Town<br>Lahore<br>Telephone number +92 42 37809948<br>Fax number +92 42 37809950<br>nadeem@acpak.com.pk<br>www.acpak.com.pk                                                                                                                                                                                |
| <b>IR</b> <b>Iran</b><br>Representative Office<br>Tamin Ehtajat Fanni Tehran (TAF Co.)<br>No. 36, West 4th St., Ettehad Ave. Damavand Rd.<br>Tehran - 1658674583, Iran<br>Telephone number +9821 77120809<br>info@taf-co.com<br>http://www.taf-co.com    | <b>KZ</b> <b>Kazakhstan</b><br>Please contact<br>Weidmüller Group<br>Russia                                                                                                                                                                                                                                                                                                                                                                                  | <b>ME</b> <b>Montenegro</b><br>Please contact<br>our Representative Office<br>Weidmüller Interface GmbH & Co. KG<br>Serbia.                                                                                                                                                                  | <b>NG</b> <b>Nigeria</b><br>Please contact<br>Weidmüller Interface GmbH & Co. KG<br>South Africa                                                                                                                                                                                                                                                                                            | <b>PL</b> <b>Poland</b><br>Weidmüller Sp. z o. o.<br>ul. Ogrodowa 58<br>00-876 Warszawa<br>Telephone number +48 22 510 09 40<br>Fax number +48 22 510 09 41<br>biuro@weidmuller.com.pl<br>www.weidmuller.pl                                                                                                                                                                                                           |
| <b>IS</b> <b>Iceland</b><br>Samey Automation Center<br>Lyngas 13<br>210 Garoabaer<br>Telephone number +354 510 5200<br>Fax number +354 5 10 5201<br>Samey@samey.is<br>www.samey.is                                                                       | <b>LB</b> <b>Lebanon</b><br>Progress Engineering & Trading Enterprises<br>Al Nahr Street<br>Beirut 11-1111<br>Telephone number +961 1 444 664<br>Fax number +961 1 561 880<br>progress@inco.com.lb                                                                                                                                                                                                                                                           | <b>MG</b> <b>Madagascar</b><br>Please contact<br>Phambili Interface<br>South Africa                                                                                                                                                                                                          | <b>NL</b> <b>Netherlands</b><br>Weidmüller Benelux B. V.<br>Franciscusweg 221<br>1216 SE Hilversum<br>P.O. Box 1505<br>1200 BM Hilversum<br>Telephone number +31 35 626 12 61<br>Fax number +31 35 623 20 44<br>info@weidmuller.nl<br>www.weidmuller.nl                                                                                                                                     | <b>PR</b> <b>Puerto Rico</b><br>Please contact<br>W Interconnections Inc.<br>United States                                                                                                                                                                                                                                                                                                                            |
| <b>IT</b> <b>Italy</b><br>Weidmüller S. r.l.<br>Via Albert Einstein 4<br>20092 Cinisello Balsamo Milano<br>Telephone number +39 02 680681<br>Fax number +39 02 6124945<br>weidmuller@weidmuller.it<br>www.weidmuller.it                                  | <b>LT</b> <b>Lithuania</b><br>Please contact<br>our Representative Office<br>Weidmüller Interface GmbH & Co. KG<br>Latvia<br><br>or<br>ELEKTROS IRANGA<br>Tinklu g. 29 a<br>LT-5319 Panevezys<br>Telephone number +370 (45) 582 828<br>Fax number +370 (45) 582 727<br>info@eliranga.lt<br><br>UAB „SLO Lithuania“<br>Vilkipėdės g. 4<br>LT-LT-03151 Vilnius<br>Telephone number +370 5 215 00 70<br>Fax number +370 5 215 00 71<br>biuras@slo.lt            | <b>MK</b> <b>Macedonia</b><br>Please contact<br>our Representative Office<br>Weidmüller Interface GmbH & Co. KG<br>Serbia<br><br>or<br>ELEKTRO - SMK dooel<br>UL. III Makedonska brigada b.b.<br>1000 Skopje<br>Telephone number +389 22460295<br>Fax number<br>Elektro-smk@telekabel.net.mk | <b>NO</b> <b>Norway</b><br>Sivilingeniør J.F. Knudtzen AS<br>Billingstadsletta 97<br>1396 Billingstad<br>PO Box 160<br>1378 Nesbru<br>Telephone number +47 66 98 33 50<br>Fax number +47 66 98 09 55<br>firmapost@jfkudtzen.no<br>www.jfkudtzen.no                                                                                                                                          | <b>PT</b> <b>Portugal</b><br>Weidmüller Sistemas de Interface S. A.<br>Estrada Outeiro Polima, R. Augusto Dias da Silva, Lote B - Esc. 2<br>São Domingos de Rana 2785-515 Abóboda<br>Telephone number +351 214 459 191<br>Fax number +351 214 455 871<br>weidmuller@weidmuller.pt<br>www.weidmuller.pt                                                                                                                |
| <b>JM</b> <b>Jamaica</b><br>Please contact<br>W Interconnections Inc.<br>United States                                                                                                                                                                   | <b>LU</b> <b>Luxembourg</b><br>Please contact<br>Weidmüller Benelux B. V.<br>Netherlands                                                                                                                                                                                                                                                                                                                                                                     | <b>MN</b> <b>Mongolia</b><br>Please contact<br>our Representative Office<br>Weidmüller Interface Azerbaijan.                                                                                                                                                                                 | <b>NZ</b> <b>New Zealand</b><br>Cuthbert S. Steward Ltd.<br>27 Te Puni Street<br>Petone<br>PO Box 38496<br>Wellington Mail Centre 5054<br>Telephone number (04) 568 6156<br>Fax number (09) 489 1752<br>csl@cuthbertstewart.co.nz                                                                                                                                                           | <b>PY</b> <b>Paraguay</b><br>Please contact<br>CPI SA<br>Argentina                                                                                                                                                                                                                                                                                                                                                    |
| <b>JO</b> <b>Jordan</b><br>Billeh Electricals Mat. Co.<br>PO Box 4343<br>Amman<br>Telephone number +962 6 4656 987<br>Fax number +962 6 4649 216                                                                                                         | <b>LV</b> <b>Latvia</b><br>SIA Abi4<br>Daugavgrivas 49 k3<br>Riga, LV-1007<br>Telephone number +371 674 70999<br>Fax number<br>abi_4@tvnet.lv                                                                                                                                                                                                                                                                                                                | <b>MT</b> <b>Malta</b><br>E. S. S., Electrical Supplies & Services Ltd.<br>San Gwakkim Road<br>Mrieħel<br><br>Telephone number +356 21255777<br>Fax number +356 21255999<br>robert.agius@ess.com.mt                                                                                          | <b>OM</b> <b>Oman</b><br>DAN INTERNATIONAL LLC.<br>Ghala St. 111<br>BP 2901<br>Seeb<br>Telephone number +968 5036 77<br>Fax number +968 5037 55<br>yedu@danintl.com                                                                                                                                                                                                                         | <b>QA</b> <b>Qatar</b><br>Doha Motors<br>PO Box 145<br><br>Telephone number +974 4651441<br>Fax number +974 4654579<br>dmtctech@qatar.net.qa<br>http://www.dohamotorsgroup.com/td.html                                                                                                                                                                                                                                |
| <b>JP</b> <b>Japan</b><br>Nihon Weidmüller Co. Ltd.<br>Sphere Tower Tennoz 2-2-8 Higashi-Shinagawa, Shinagawa-ku<br>Tokyo<br>140-0002<br>Telephone number +81 3 6711 5300<br>Fax number +81 3 6711 5333<br>info@weidmuller.co.jp<br>www.weidmuller.co.jp | <b>RO</b> <b>Romania</b><br>Representative Office<br>Weidmüller Interface GmbH & Co. KG<br>Ionescu Crum Street, No. 1, 1st Tower, 1st Floor, Office 4<br>500446 Brasov - Brasov Business Park<br>Telephone number +40 (268) 446 222<br>Fax number +40 (268) 446 224<br>claudiu.totea@weidmuller.com<br>www.weidmuller.ro                                                                                                                                     | <b>MU</b> <b>Mauritius</b><br>Mubelo Electrical Ltd.<br>Office 26, Gateway building, St Jean Road<br>Quatre Bornes<br>Mauritius<br>Telephone number +230 4670989<br>Fax number +230 4654051<br>richard.mubelo@orange.mu                                                                      | <b>PE</b> <b>Peru</b><br>IMPEXINCA S.A.C.<br>Calle Ortiz de Zevallos No. 105, Urb. San Antonio 18<br>Lima, Miraflores<br>Telephone number +51 1 447 5608<br>info@impexinca.pe<br>www.impexinca.pe<br><br>J & W CIA. S. A.<br>Calle 6 Mz. D Lte. 23, Urb. Ind. Grimanesa 01<br>Callao<br>Telephone number +51 1 572 2539<br>Fax number +51 1 572 0152<br>contacto@jwcia.com<br>www.jwcia.com | <b>RS</b> <b>Serbia</b><br>Representative Office<br>Weidmüller Interface GmbH & Co. KG<br>Ustanicka 189, III sprat lokal 7a<br>11050 Beograd<br>Telephone number +381 112885274<br>Fax number +381 112885274<br>zoran.rabrenovic@weidmuller.com<br><br>TeLa Elektrik d.o.o.<br>Ul. Dr. Drage Ljocić 6<br>Beograd<br>Telephone number +381 11 2772 415<br>Fax number +381 11 2772 850<br>office@tela.rs<br>www.tela.rs |
| <b>KE</b> <b>Kenya</b><br>Please contact<br>our Representative Office<br>Weidmüller Interface GmbH & Co. KG<br>South Africa.                                                                                                                             | <b>MA</b> <b>Morocco</b><br>Sofimed<br>137, Bd Moulay Ismail Roches Noires<br>20290 Casablanca<br>Telephone number<br>Fax number<br>contact@sofimedmaroc.com                                                                                                                                                                                                                                                                                                 | <b>MX</b> <b>Mexico</b><br>W Interconnections S. A.<br>DE C. V.<br>Blvd. Hermanos Serdán 698, Col. San Rafael Oriente 72029 Puebla<br>Telephone number +52 (222) 268 6227<br>Fax number +52 (222) 286 6242<br>clientes@weidmuller.com.mx                                                     | <b>PH</b> <b>Philippines</b><br>Enclosure Systems Specialists Inc.<br>2276 Don Chino Roces Avenue Extension<br>Room 103/105 Narra Building<br>1231 Makati City<br>Telephone number +63 2 813 8580<br>Fax number +63 2 813 8596<br>sales_encsys@pltdsl.net<br>www.enclosuresystemsph.com                                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                                       |
| <b>KG</b> <b>Kyrgyzstan</b><br>Please contact<br>our Representative Office<br>Weidmüller Interface Azerbaijan.                                                                                                                                           |                                                                                                                                                                                                                                                                                                                                                                                                                                                              | <b>MY</b> <b>Malaysia</b><br>Connect Plus Technology Sdn Bhd<br>No. 43, Jalan PJS 11/22, Bandar Sunway<br>46150 Petaling Jaya<br>Selangor Darul Ehsan<br>Telephone number +60 3 5633 7363<br>Fax number +60 3 5633 6562<br>paul@cptech.com.my<br>www.cptech.com.my                           |                                                                                                                                                                                                                                                                                                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                       |
| <b>KR</b> <b>Korea</b><br>Weidmüller Korea Co. Ltd.<br>9th floor<br>429, Teheran-ro, Gangnam-Gu Seoul 135-721<br>Telephone number +82 2-516-0003<br>Fax number +82 2-516-0090<br>info@weidmuller.co.kr<br>www.weidmuller.co.kr                           |                                                                                                                                                                                                                                                                                                                                                                                                                                                              | <b>MZ</b> <b>Mozambique</b><br>Please contact<br>Phambili Interface<br>South Africa                                                                                                                                                                                                          |                                                                                                                                                                                                                                                                                                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                       |

# Addresses worldwide

Let's connect.

- RU Russia**  
Weidmüller Group  
7/10 Khlebozavodskiy  
Passage,  
Moskau  
115230  
Telephone number +7 495  
280 72 71  
Fax number +7 495 280  
72 71  
Info@weidmueller.ru  
www.weidmueller.ru
- SA Saudi Arabia**  
Al Abdulkarim Holding Co.  
P.O. Box 4  
Dammam 31411  
Telephone number +966 3  
8337 110  
Fax number +966 3  
8829547  
E-mail salehsk@akh.com.sa  
www.weidmueller.ae  
  
Saudi Electric Supply  
Company (SESCO)  
P.O. Box 32 98  
Al Khobar 31952  
Telephone number +966 3  
8829546 Ext. 3030  
Fax number  
E-mail Safdar.Malik@sescogex.com  
www.sesco-gex.com
- SE Sweden**  
Weidmüller AB  
Axel Danielssons väg 271  
BOX 31025  
SE-200 49 Malmö  
Telephone number +46 77-  
143 00 44  
Fax number +46 40-37 48 60  
info@weidmuller.se  
www.weidmuller.se
- SG Singapore**  
Weidmüller Pte. Ltd.  
70 Bendemeer Road  
# 04-03 Luzerne Building  
Singapore 339940  
Telephone number +65 6841  
5311  
Fax number +65 6841 5377  
info@weidmuller.com.sg  
www.weidmuller.com.sg
- SI Slovenia**  
Elektrospoji d. o. o.  
Stegne 27  
Sl- 1000 Ljubljana  
Osrednjeslovenska  
Telephone number +386 1  
511 3810  
Fax number +386 1 511  
1604  
info@elektrospoji.si  
www.elektrospoji.si
- SK Slovakia**  
ELEKTRIS s.r.o.  
Elektrárenská 1  
831 04 Bratislava  
Telephone number +421  
2/4920 0113  
Fax number +421 2/4920  
0119  
bratislava@elektris.sk
- SV El Salvador**  
Prestegard Electro  
11 Avenida Norte No. 240  
Edificio Salazar No. 2  
San Salvador  
Telephone number +503  
2271 1690  
Fax number +503 2221  
3851  
prestegard@navegante.com.sv
- SY Syria**  
Please contact  
Weidmuller Middle East FZE  
United Arab Emirates
- SZ Swaziland**  
Please contact  
Phambili Interface  
South Africa
- TH Thailand**  
Pisanu Engineering Co. Ltd.  
Kwang Dingaeng, Khet  
Dingaeng  
800/2 Soi Trakulsuk, Asoke-  
dindaeng Road  
Dindaeng, Bangkok  
10400  
Telephone number +66 2  
248 2896  
Fax number +662 105 6301  
ecsales@pisanu.co.th  
www.pisanu.co.th  
  
Representative Office  
Weidmüller Pte. Ltd.  
37/F, Sathorn Square Building  
98 North Sathorn Road  
Bangkok, Silom Bangrak  
10500  
Telephone number +66 2  
105 6300  
Fax number +66 2 642 9220  
info@weidmuller.com.sg
- TJ Tajikistan**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.
- TM Turkmenistan**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.
- TN Tunisia**  
Please contact  
Weidmüller E. U. R. L.  
France
- TR Turkey**  
Weidmüller Elektronik Ticaret  
Ltd. Sirketi  
Kavacik Mah. Orhan Veli Kanik  
Caddesi 9/1  
34810 Beykoz / Istanbul  
Telephone number +90 (216)  
537 10 70  
Fax number +90 (216) 537  
10 77  
info@weidmuller.com.tr  
www.weidmuller.com.tr
- TW Taiwan**  
Please contact  
Weidmuller (Hong Kong)  
Limited Co. Ltd.  
Hong Kong
- TZ Tanzania**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
South Africa.
- UA Ukraine**  
LLC WM UKRAINE  
Levanevskogo str. 6  
Kiev  
3058  
Telephone number +38 044  
490 32 48  
Fax number  
info@wm-ua.com.ua  
wm-ua.com.ua/  
  
Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Z, office 303  
7-D, Zdolbunivska str.  
Kiev, 2081  
Telephone number  
(mobile) +38 050 440 25 24  
info.ua@weidmueller.com
- US United States**  
W Interconnections Inc.  
821 Southlake Boulevard  
Richmond Virginia 23236  
Telephone number +1 (804)  
794-2877  
Fax number +1 (804) 379-  
2593  
info@weidmuller.com  
www.weidmuller.com
- UY Uruguay**  
REWO Uruguay S. A.  
AV. Bolivia 2001Esq  
Roca fuerte  
11300 Carrasco Montevideo  
Telephone number +598  
2604 8439  
Fax number +598 2604  
8439  
rewo@rewouruguay.com.uy
- UZ Republic of Uzbekistan**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.
- VE Venezuela**  
Somerinca C. A.  
Corazon de Jesus - 3ra  
Transversal con calle el  
Carmen- Los Dos Caminos  
Caracas 1070-A  
Telephone number +58  
2122352748  
Fax number +58  
2122399341  
klocmoeller@cantv.net  
www.somerinca.com
- VN Vietnam**  
AUMI Industrial Equipment &  
Automation Company Limited  
E1, La Thanh Hotel  
218 Doi Can Street  
Lieu Giai Ward, Ba Dinh  
District  
Hanoi City  
Telephone number +84 4  
37628601  
Fax number +84 4  
62661391  
aumi@aumi.com.vn  
www.aumi.com.vn  
  
Representative Office  
Weidmüller Pte. Ltd.  
Level 16 Saigon Tower  
Building  
29 Le Duan Street  
District 1  
Ho Chi Minh  
Telephone number +848  
3520 7717  
Fax number +848 3520  
7604  
info@weidmuller.com.sg
- ZA South Africa**  
Phambili Interface  
PO Box 193  
1609 Johannesburg, Edenvale  
5 Bundo Road, Sebenza  
1610 Johannesburg  
Telephone number +27 (11)  
4521930  
Fax number  
info@weidmuller.co.za  
www.weidmuller.co.za  
  
Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
210 Amarand  
Avenue, Pegasus Building  
181 Pretoria, waterkloof Glen  
ext 2 -  
Telephone number +27 12  
003 2906  
Fax number +27 (11)  
4526455  
Jacques.Vosloo@weidmueller.  
com  
www.weidmueller.com
- ZM Zambia**  
Please contact  
Phambili Interface  
South Africa
- ZW Zimbabwe**  
Please contact  
Phambili Interface  
South Africa

