



ENGLISH

Datasheet

Telephone Slide LED Indicator Lamp

RS Stock number 204-192

Dimensions (mm):

Specifications:

LED/Multiled	LED
Mounting Size	-
Mounting Finish	-
Protection	-
Mount Holder	T6.8 Slide Base
Chip Qty	1
Indicator Colour	Red
Optimum Voltage (V)	48V dc
Rectifier	-

AC Current	-
DC Current	15mA
Voltage Tolerance	10%
Optimum Temperature	-30°C ... +60°C
Storage Temperature	-30°C...+60°C
Contact Tab	T6.8 Slide bar
Wavelength (nm)	630
Intensity	250mcd